

24VDC ELECTRONIC NON-DIMMABLE POWER SUPPLIES

**24
VOLT**

NON-DIMMABLE

**5 Yr.
WARRANTY**

**ETL
Intertek**

PRODUCT DESCRIPTION

LTP Series Cord and Plug 24VDC Electronic LED Power Supplies feature LED indicator for 'power on' and 5 year warranty. Each LTP Electronic Power Supply incorporates short circuit, over-voltage and over-temperature protection.

LTH Series Hardwire 24VDC Electronic LED Power Supplies feature 100-240V A/C input, LED indicator for 'power on' and 5 year warranty. Each LTH Electronic Power Supply incorporates short circuit, over-voltage and over-temperature protection.



LTP SERIES KEY FEATURES

- Class 2
- Overload, short-circuit and temp. protection

LTH SERIES KEY FEATURES

- 120V A/C input
- Overload, short circuit and temp. protection

ORDERING INFORMATION

Catalog No.	Description	Watts	Weight	Dimensions
LTP24-48	24VDC - 48W - 2 amps - 120V - 120V Cord (72") and plug. Short circuit, overload protection - LED indicator for power on. UL listed.	48W	1.8 lbs.	4.68"L x 2.05"W x 1.25"H
LTP24-90	24VDC - 90W - 3.75 amps - 120V - Cord (72") and Plug Short circuit, overload protection - LED indicator for power on. UL listed	90W	1.8 lbs.	5.75"L x 2.375"W x 1.25"H
LTH24-2*	24VDC - 24W - 1.2 amps - 120V Short circuit, overload protection - LED indicator for power on. RU listed.	24W	6.9 oz.	3-3/16"L x 2"W x 1-1/8"H
LTH24-4*	Hardwire 24VDC - 100W - 4.2 amps - 100-240VAC Input - Short circuit, overload protection - LED indicator for power on Metal chassis with screw terminals and mounting feet 2 sets of DC screw terminals. RU listed.	100W	1.6 lbs.	7"L x 3.875"W x 1.75"H
LTH24-8*	Hardwire 24VDC, - 200W - 8.4 amps - 120V - 100-240VAC Input Short circuit, overload protection - LED indicator for power on Metal chassis with screw terminals and mounting feet 2 sets of DC screw terminals. RU listed.	200W	2.0 lbs.	7.84"L x 3.90"W x 1.97"H
LTH24-13	Hardwire 24VDC - 300W - 85-264 VAC input - 47-63Hz frequency range at 83% typical efficiency.	300W	2.0 lbs.	9"L x 4"W x 2"H
DPPS-12-24V	24VDC - 12W - Class 2 with cord and plug for LARC6 and Slim Edge™ only	12W	8 oz.	2.75"L x 2"W x 1"H
DPPS-36-24V	24VDC - 36W - Class 2 with cord and plug for LARC6 and Slim Edge™ only	36W	12 oz.	4"L x 1-3/4"W x 1.125"H

* Recommended for commercial applications. Enclosure by others required.
Please see our website for updated power supply specifications and information. 5 year warranty.