SCREW, NUT, MULTI & ADJUSTABLE



As the tradesperson's needs change, so do Klein's products. The latest additions to our line of drivers feature added functionality to increase productivity and decrease the number of tools on the belt or in the bag.



4-IN-1 ELECTRONICS SCREWDRIVERS



Four different bits in one tool

- Rotating cap for optimum and precise control
- Heat-treated precision machined tip for greater strength

Cat. No.	Tips	Overall Length
32581	#0 & #00 Phillips and 1/8" & 3/32" Slotted	6.5" (165 mm)
32585	T7, T8, T10 and T15 tamper-proof TORX®	6.5" (165 mm)



Completely hollow handle for unlimited threaded rod lengths

- · Wrench assist for additional torque
- · Magnetic feature helps grab hex nuts securely









Multiple sizes in one convenient tool

- Interchangeable hex sizes are available in two models
- Heavy duty handles and shafts exceed the torque performance of regular nut drivers
- · Wrench assist feature for additional torque

Cat. No.	Hex Sizes	Overall Length
32800	3/16", 1/4", 5/16", 3/8", 7/16" & 9/16"	9.5" (241 mm)
32801	3/16", 1/4", 5/16", 3/8" & 9/16"	9.1" (231 mm)





Ratcheting mechanism allows user to work faster and with more efficiency

• Includes four different screwdriver bits and 1/4" and 5/16" nut drivers

Cat. No.	Tips	Hex Sizes	Overall Length
32593	#1 & #2 Phillips and 1/4" & 3/16" Slotted	1/4"	3.5"
32594	#1 & #2 Square, #2 Phillips & 3/16" Slotted	& 5/16"	(63.5 mm)

6-IN-1 RATCHETING STUBBY SCREWDRIVERS





Fixed shaft and internal storage compartment for the bits so they stay with the driver

• These drivers include 14 different screwdriver tips plus a 1/4" nut driver

Cat. No.	Description	Tips	Overall Length
32290	15-in-1 Classic	#0, #1, #2, #3 Phillips; #1 and #2 Square; #1 and #2 Combo; #10, #15, #20, #25 Torx; 4 and 6 MM Slotted; ¼" Hex	
32291	15-in-1 Tamperproof	#10, #15, #20, #25, #27, #30 Torx-Pins; 1/8", 9/64", 5/32", 3/16" Hex-Pins; #6, #8, #10, #12 Spanners; ¼" Hex	9" (229 mm)
32292	15-in-1 HVAC	#0, #1, #2 and #3 Phillips; #1 and #2 Square; Schrader Valve Insertion and Core Removal Bits; #10, #15, #20 and #25 Torx; 4 and 6 MM Slotted; '4" Hex	




Adjust to the length you need on the fly

Carry fewer tools with a more versatile screwdriver. The shafts adjust anywhere from 4" to 8" (10-20 cm) for numerous length choices.

- Removable and reversible shafts with a different tip on each end
- Proprietary system securely holds the blade in place as durable as a traditional Klein fixed blade screwdriver
- Use on internet boxes, telecomm boxes, generators and more

Cat. No.	Description	Tips	
32708	Adjustable Length Screwdriver	#1 & #2 Square	
32751	Adjustable Length Screwdriver	#2 Phillips & 1/4" Slotted	
Sets Replacement Blades			
32618	Replacement Blades	#2 Phillips and 1/4" Slotted	
32709	Replacement Blades	#1 & #2 Square	
32713	Replacement Blades	#1 Phillips & 3/16" Slotted	
32715	Replacement Blades (3-Pack)	#2 Phillips & 1/4" Slotted #1 Phillips & 3/16" Slotted #1 & #2 Square	
32619	Handle only	N/A	

ADJUSTABLE LENGTH SCREWDRIVERS





See our complete line of **Drivers**

www.kleintools.com/catalog/drivers

