




# SLIMLED<sup>TM</sup>MULTI

## WITH 5-POSITION SELECTABLE CCT

**MULTI-APPLICATIONS, SELECTABLE TEMPERATURE, MULTI-COLORS, NOT SOLD SEPARATELY .**

With the SLIMLED MULTI you can easily convert a standard Octagon Box into a recessed downlight and have the capabilities to retro-fit a traditional 4" downlight to a LED fixture. SLIMLED MULTI also combines functionality with design as there is a selectable CCT switch to allow temperature selectability on site, as well as being packaged and sold with three different colored trims that are magnetically interchangeable for a look that will suit any location. With a built-in driver for easy installation, upgrading to a SLIMLED fixture is the obvious choice!



**2700K**  
SOFT WHITE

**3000K**  
WARM WHITE

**3500K**  
NEUTRAL WHITE

**4000K**  
COOL WHITE

**5000K**  
DAYLIGHT



**USER  
SELECTABLE  
COLOUR  
TEMPERATURES**

UP TO  
**550 LUMENS**  
8W / 120V



Liteline Corporation  
Copyright © 2019  
All rights reserved.


Telephone  
416.996.1856  
1.866.730.7704

Fax  
905.709.5255  
1.888.738.9736

[LITELINE.COM](http://LITELINE.COM)

REV 10.03.2019

# EVERYTHING IN 1 BOX:



Built-in driver

Dimmable



Selectable CCT  
5 positions

Wet location and fire-rated\*

E26 Base adaptor\*\*

Butterfly mounting clips\*\*

Dead front

Plastic trims:

- 3 colors shipped in 1 box
- Magnetically interchangeable
- Square options available

\*Fire-rated when used in a fire-rated Octagon Box  
\*\* Used when mounted to a compatible 4" recessed housing

## SLIMLED MULTI OVERVIEW:

### MOUNTING:

For use with a standard Octagon Box or 4" recessed housing



### BODY:

On-face magnets secures one of three included dead front magnetic trims



### TRIMS:

Packaged and sold with 3 plastic trims:

- White
- Silver
- Black

Square options sold separately



## FEATURES:

- Selectable CCT (27 K, 30 K, 35 K, 40 K, 50 K)
- Fire-rated when used in a fire-rated Octagon Box
- Wet Location Rated
- Dead Front
- Includes three interchangeable magnetic trims: white, black, and silver
- Up to 550 lumens
- 90 CRI
- 8 Watts / 120V
- Air tight
- Built-in driver
- Dimmable



### COMPATIBLE HOUSINGS:

- RF401 series    **OR**    • Standard octagon box
- RF402 series
- RF405 series

**ORDERING:** SLMT4-8W

