PASS & SEYMOUR®

USB CHARGER DEVICES



MOBILE. READY.







CHARGE MULTIPLE MOBILE DEVICES FROM ONE USB RECEPTACLE — **WITHOUT AN ADAPTER.**





Legrand offers a full line of Pass & Seymour® charging solutions designed to power up mobile devices quickly and reliably — without the need for bulky AC adapters. From USB-only receptacles to USB/receptacle/switch combos, these 4.2-, 3.1- and 2.1-amp devices:

- Charge multiple USB-powered devices at the same time
- Allow users to plug USB cable directly in wall without AC adapter
- Accept standard Pass & Seymour Wall Plates
- Include back and side wiring terminals for installation flexibility
- Are available in all Pass & Seymour Decorator-style colors
- Are compatible with USB 2.0 and 3.0 devices

DEVICE COMPATIBILITY

iPad

iPhone

iPod

Tablets

Smartphones

Handheld Video Game Systems

Bluetooth Headsets

Digital Cameras

e-Readers

GPS

Much more



TM8USBWCC6

USB Charger with Tamper-Resistant Receptacle

Two USB "A" style charging outlets plus a 15-amp tamper-resistant receptacle

Charge two tablets simultaneously while still using receptacle

Total charging capacity of 2.1 amps

Available in Residential, Fed Spec Grade and Hospital Grade models



TM8USB4WCC6

Quad USB Charger

Four USB ports

Can charge four tablets simultaneously

Total charging capacity of 4.2A



TM826USBWCC6

USB Charger with Duplex Decorator Tamper-Resistant Receptacle

Two USB "A" style charging outlets plus a duplex 15-amp tamper-resistant receptacle

Charge two tablets simultaneously while still using receptacles

Total charging capacity of 3.1 amps

Available in Residential, Fed Spec Grade and Hospital Grade models



TM83USBWCC6

USB Charger with Single Pole/3-Way Switch

Flexible wiring allows switch to control light load or USB outlets

Convenient operation — combines ON/OFF Decorator-style switch with two separate USB ports for charging



IDEAL FOR RESIDENTIAL, COMMERCIAL, AND HEALTH CARE APPLICATIONS, INCLUDING:

Kitchens
Bedrooms
Home Offices
Airport Lounges
College Dorms
Hotels/Hospitality
Common Study Areas
Open Work Spaces
Meeting Rooms
Office Cubicles
Patient Rooms
Nurses' Stations
Labs
Desk Areas

designed to be better."









TR8300HUSBW

PART NO.	DESCRIPTION	RAT A.	INGS V.	COLORS	VDC	Charging Capacity (A)
TM8USB*CC6	2 USB Chargers and Tamper-Resistant Receptacle	15	125	BK, I, LA, NI, TI, W	5	2.1
TM88USB*	2 USB Chargers and Single Tamper-Resistant Receptacle	15	125	BK, I, LA, NI, W	5	3.1
TR5261USB*	Fed Spec Grade — 2 USB Chargers		125	BK, I, LA, NI, W,	5	2.1
TR5361USB*	and Tamper-Resistant Receptacle	20	125	RED, GN, -, GRY	5	2.1
TR8201USB*	Hospital Grade — 2 USB Chargers and	15	125	BK, I, LA, NI, W,	5	2.1
TR8301USB*	Tamper-Resistant Receptacle		125	RED, -, GRY	5	2.1
TM83USB*CC6	2 USB Chargers with Single Pole/3-Way Switch	15	120	BK, I, LA, NI, W	5	2.1
TM8USB4*CC6	Quad USB Charger			BK, I, LA, NI, W	5	4.2
TM826USB*CC6	2 USB Chargers and Duplex Decorator Tamper-Resistant Receptacle	15	125	BK, I, LA, NI, W	5	3.1
TR5262USB*	Fed Spec Grade — 2 USB Chargers and	15	125	BK, I, LA, NI, W,	_	2.1
TR5362USB*	Duplex Tamper-Resistant Receptacle		125	RED, GN, -, GRY	5	3.1
TR8200HUSB*	Hospital Grade — 2 USB Chargers and		125	BK, I, LA, NI, W,	5	3.1
TR8300HUSB*	Duplex Tamper-Resistant Receptacle	20	125	RED, –, GRY	J	3.1

*COLOR DESIGNATION						
BK	Black	RED Red				
1	lvory	GN	Green			
LA	Light Almond	-	Brown			
NI	Nickel	GRY	Gray			
W	White					



Electrical Wiring Systems

P.O. Box 4822 Syracuse, NY 13221-4822 800.776.4035 www.legrand.us/PassandSeymour

570 Applewood Crescent Vaughan, Ontario L4K 4B4 905.738.9195 www.legrand.ca

