Red Dot Weatherproof nonmetallic covers

Code Keeper extra-duty nonmetallic weatherproof while-in-use covers



CKPM-C-CN



2CKPM-C-CN

One cover handles GFCI, single, duplex or switch configurations

Red Dot Code Keeper extra-duty nonmetallic weatherproof while-in-use covers make it easier than ever to comply with Canadian Electrical Code (CEC) requirements for receptacles in wet locations. Weatherproof covers are often subject to bumps and impact through everyday use, but this reinforced design withstands abuse, featuring a stainless steel hinge pin for rugged cover attachment that's great for high-traffic areas.

Pre-configured for GFCI, each cover ships with adapter plates to accommodate single or duplex receptacles and switches. Now, contractors can handle any application they encounter without needing dozens of different covers.

- Complies with CEC Rule 26-708(2) for extraduty outlet box hoods – required in wet locations (area 1)
- Robust stainless steel hinge pin ideal for hightraffic areas
- Available in single- and two-gang configurations with a variety of cover depths
- Accommodates numerous receptacle configurations and almost every common plug and cord size
- Keyhole mounts make it fast and easy to install just loosen existing device screws and slide cover over
- Combination box or device-mounting design provides flexibility in installation
- · Lockable for security, whether in use or not
- Ships with adapter plates and pre-mounted gaskets
- Unique wasp guard included to keep out unwanted pests

Red Dot Code Keeper extra-duty nonmetallic while-in-use covers






Cat. no	Top colour	Bottom colour	Std. ctn.
Single-gang shallow – vertical or	horizontal – 2¼" deep		
CKPS-C-CN	Clear	Grey	7
CKPS-G-CN	Grey	Grey	7
CKPS-W-CN	White	White	7
CKPS-BR-CN	Bronze	Bronze	7
Single-gang medium – vertical o	r horizontal – 2%" deep		
CKPM-C-CN	Clear	Grey	6
CKPM-G-CN	Grey	Grey	6
CKPM-W-CN	White	White	6
CKPM-BR-CN	Bronze	Bronze	6
Single-gang large – vertical or ho	orizontal – 4¾" deep		
CKPL-C-CN	Clear	Grey	4
Two-gang medium – 2½" deep			
2CKPM-C-CN	Clear	Grey	4
2CKPM-G-CN	Grey	Grey	4
2CKPM-W-CN	White	White	4
2CKPM-BR-CN	Bronze	Bronze	4
Two-gang large – 4¾" deep			
2CKPL-C-CN	Clear	Grey	4

Red Dot nonmetallic covers

Code Keeper universal nonmetallic weatherproof while-in-use covers



Single-gang base options GFCI, duplex, switch, up to $1\% \ensuremath{\mathrm{g}}$ rounds

Two-gang base options GFCI, duplex, switch and $1^3\!/_{\! 8}$ round receptacle