Red Dot Weatherproof products

FS and FD metallic covers

Single-gang horizontal covers (cast aluminum)

Cat. no.

CCD-FS



Grey – box mount (zinc)



| | | 31119 |
|--------------|------|-------|
| | Std. | Cat |
| Description | ctn. | CCI |
| mount (zinc) | 50 | CFS |
| | | CW |
| | | Dia |





CCD-FS

Single-gang horizontal covers (cast aluminum)



| Cat. no. | Α | В | F | G | K | L |
|----------|--------|------|-------|------|------------------------------------|--------|
| CCD-FS | 213/16 | 4%16 | 11//8 | 31/4 | - | _ |
| CFSH-G | 213/16 | 4%16 | 11//8 | 31/4 | 1 ¹¹ / 32 | 221/32 |
| CWPDR-FS | 213/16 | 4%16 | 11//8 | 31/4 | - | - |

agrams







Single-gang horizontal covers (cast aluminum)



box mount



| Single-gang vertical covers (cast aluminum | | | |
|--|--|--|--|
| | | | |



| | Cat. no. | Description | Std. ctn. |
|--------|----------|------------------------------------|--------------|
| CFSR-G | CFSR-G | One GFCI receptacle – box mount | 25 |

| | | | Nominal | Max. device | Std. |
|-----------------|----------|----------------------------------|------------|----------------|------|
| | Cat. no. | Description | size (in.) | face dia. | ctn. |
| CFSR Series* | CFSR-L | Single receptacle – box mount | 1%16 | 1.600 | 25 |
| | | | | | |

*Gasket and screws included.

Single-gang (cast aluminum)



| | Cat. no. | Description | Std. ctn. |
|------|----------|------------------|--------------|
| CFSB | CFSB | Blank, box mount | 100 |
| | | | |



Red Dot Weatherproof products

FS and FD metallic covers


Single-gang vertical covers (cast aluminum)





| Cat. no. | Α | В | F | G | К | L |
|----------|------|--------|------|-------|--------|--------|
| CFSR-G | 4%16 | 213/16 | 31/4 | 11//8 | 221/32 | 111/32 |

Diagram










| Cat. no. | А | В | F | G |
|----------|------|--------|------|-------|
| CFSR-L | 4%16 | 213/16 | 31/4 | 11//8 |

Diagram



CFSR Series*

^{*}Gasket and screws included.

Red Dot Weatherproof products

Deck grommet and stainless steel box and cover



Nonmetallic deck grommet

| Cat. no. | Finish |
|----------|--------|
| DKG-CA | Black |

All supplied receptacles are tamper-resistant



- 37.3 cu. in. capacity
- 316 stainless steel construction
- NEMA 3R rated
- NEMA 4X rated while not in use when properly installed
- NSF certified
- cULus Listed

Stainless steel while-in-use box and cover system





| | | Std. |
|----------|---|------|
| Cat. no. | Description | ctn. |
| SSE | Stainless steel while-in-use box and cover system | 1 |