

ON-Q® Plastic Media Enclosures and Accessories



Centralized Distribution for Wired & Wireless Low Voltage Systems

20 Inch Plastic Enclosure with Cover & Trim 30 Inch Plastic Enclosure with Cover & Trim 42 Inch Plastic Enclosure with Cover & Trim

This enclosure secures both structured wiring systems and wireless networking equipment in a professional, out-of-sight installation.

Enclosures: Features & Benefits

- Wireless Transparent Material UL-rated ABS plastic allows wireless devices such as wireless routers, access points or service provider equipment to secure in the cabinet without degrading network performance.
- **Stackable** Enclosures and doors are each neatly stackable to efficiently ship and warehouse.
- Surface or Flush Mounting Mounts inside a stud bay for a flush finish to wall surface or can be surface mounted.
- **UL Rated** Meets or exceeds the standards of UL Standard 2416. Specified for non-fire rated walls.
- Universal Mounting Grid Compatible with video, voice and data distribution modules from multiple manufacturers. Ask us for our up-to-date compatibility list.
- Extensive Venting Provides superior heat dispersion for powered devices mounted in the enclosure.
- Extra Depth Hinged Door and Trim add 1.2" (30mm) of enclosure depth for compatibility with more third party devices such as uninterruptable power supplies (UPS).
- Conceals Drywall Cutout Trim Ring conceals the drywall cutout for a professional finish. The reversible Hinged Door attaches to the trim ring and can swing a full 180 degrees.
- Locking Enclosure Locking can be accomplished with the provided screw holes, or a keyed lock may be purchased separately as an option (364478-01)





Enclosure Size	Complete Assembly Enclosure with Hinged Door & Trim	Hinged Door & Trim (Single)	Hinged Door & Trim (5 Pack)	Enclosure Only (Single)	Enclosure Only (5 Pack)
20 Inch	ENP2050-NA	ENP2060-NA	ENP20605-NA	ENP2080-NA	ENP20805-NA
30 Inch	ENP3050-NA	ENP3060-NA	ENP30605-NA	ENP3080-NA	ENP30805-NA
42 Inch	ENP4250-NA	ENP4260-NA	ENP42605-NA	ENP4280-NA	ENP42805-NA
















Compliance

- UL 985, Household Fire-Warning System Units. ULC-S545, Residential Fire Warning System Control Units
- UL 1023, Household Burglar-Alarm System Units. CAN/ULC/ORD-C1023, Household Burglar Alarm System Units
- UL 2416, Audio/Video, Information and Communication Technology Equipment Cabinet, Enclosure and Rack Systems
- UL60950-1 & CAN/CSA C22.2 No. 60950-01-07, Information Technology Equipment, Including Electrical Business Equipment
- RoHS Compliant



Accessories

Plastic Enclosure Accessory	Universal Mounting Plate	Fiber Management Spools	Cable Management Clips (20 Pack)	2" Rubber Grommet (5 Pack)	Optional Keyed Lock
	AC1040	AC1041	AC1035-20	AC1034	364478-01











Features & Benefits

AC1040

- 3rd Party Devices Allows 3rd party wired and wireless devices to be secured within structured wiring enclosure
- Multiple Mounting Options Vertical and horizontal strapping locations provide a variety of mounting configurations
- **Secure** Strategically places screw holes allow devices to be securely affixed within enclosure
- Mounting Hardware Includes (4) plungers and grommets and 4' of Velcro strapping – accepts 1/2" Velcro or cable ties

AC1041

- Stay Organized Neatly organize and manage fiber within structured wiring enclosure
- **Bend Radius Protection** 1.5" spool radius maintains proper bend requirements for fiber and category cable
- **Versatile Installation Options** Half round design and multiple mounting holes provide versatile installation options for metal or plastic enclosures
- Mounting Hardware Sold as a pair and includes (4) plungers and grommets and (2) 4" cable ties

AC1035-20

- Clean Installations Harness cables within a plastic enclosure for clean installations
- No Tools Necessary Easily attach to the plastic enclosure with included plunger/grommet
- Secure Clips mount securely to enclosure, withstanding 20 lbs pull force
- Materials Pack includes 20 Cable Management Clips

AC1034

• Local Compliance – Local Compliance - 2" Grommet Pack (5) seals knockout when necessary for compliance with local jurisdictions.

364478-01

 Secure – Keep contents locked and secure with the optional keyed lock for plastic enclosures

AC1040


























AC1040 - Universal Mounting Plate






AC1041 - Fiber Management Spools



AC1035-20 - Cable Management Clips





NOTE: The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.



Legrand, North America 60 Woodlawn Street West Hartford, CT 06110 1.877.BY.LEGRAND (295.3472) www.legrand.us

9024 Keele Street Concord ON, L4K 2N2 905.738.9195 www.legrand.ca