




## Circuit Guard®, Specification Grade Duplex Receptacles



Description	Color	Catalog Number	
Surge protection receptacles with light, 240 joules, 15kA peak current.	Blue	<b>HBL5260SA</b>	<b>HBL5360SA</b>
	Ivory	<b>HBL5260ISA</b>	<b>HBL5360ISA</b>
	Office White	<b>HBL5260OWSA</b>	<b>HBL5360OWSA</b>
	White	<b>HBL5260WSA</b>	<b>HBL5360WSA</b>
Surge protection receptacles with light and alarm, 240 joules, 15kA peak current.	Blue	<b>HBL5262SA</b>	<b>HBL5362SA</b>
	Gray	<b>HBL5262GYSA</b>	<b>HBL5362GYSA</b>
	Ivory	<b>HBL5262ISA</b>	<b>HBL5362ISA</b>
	Office White	<b>HBL5262OWSA</b>	<b>HBL5362OWSA</b>
	White	<b>HBL5262WSA</b>	<b>HBL5362WSA</b>
Isolated ground, surge protection receptacles with light and alarm, 240 joules, 15kA peak current.	Blue	<b>IG5262SA</b>	<b>IG5362SA</b>
	Gray	<b>IG5262GYSA</b>	<b>IG5362GYSA</b>
	Ivory	<b>IG5262ISA</b>	<b>IG5362ISA</b>
	Office White	<b>IG5262OWSA</b>	<b>IG5362OWSA</b>
	Orange	<b>IG5262OSA</b>	<b>IG5362OSA</b>
White	<b>IG5262WSA</b>	<b>IG5362WSA</b>	
4-PLEX® surge protection receptacles with lights, 80 joules, 6.5kA peak current.	Blue	<b>HBL415S</b>	<b>HBL420S</b>
	Ivory	<b>HBL415IS</b>	<b>HBL420IS</b>



## Circuit Guard®, Hospital Grade Duplex Receptacles


Description	Color	Catalog Number	
Surge protection receptacles with light and alarm, 240 joules, 15kA peak current.	Blue	<b>HBL8262SA</b>	<b>HBL8362SA</b>
	Gray	<b>HBL8262GYSA</b>	<b>HBL8362GYSA</b>
	Ivory	<b>HBL8262ISA</b>	<b>HBL8362ISA</b>
	Red	<b>HBL8262RSA</b>	<b>HBL8362RSA</b>
	White	<b>HBL8262WSA</b>	<b>HBL8362WSA</b>
Isolated ground, surge protection receptacles with light and alarm, 240 joules, 15kA peak current.	Blue	<b>IG8262SA</b>	<b>IG8362SA</b>
	Gray	<b>IG8262GYSA</b>	<b>IG8362GYSA</b>
	Ivory	<b>IG8262ISA</b>	<b>IG8362ISA</b>
	Orange	<b>IG8262OSA</b>	<b>IG8362OSA</b>
	Red	<b>IG8262RSA</b>	<b>IG8362RSA</b>
White	<b>IG8262WSA</b>	<b>IG8362WSA</b>	
4-PLEX surge protection receptacles with lights, 80 joules, 6.5kA peak current.	Blue	—	<b>HBL420HS</b>
	Ivory	—	<b>HBL420HIS</b>
	Red	—	<b>HBL420HRS</b>

## 4-PLEX® Accessories


Description	Color	Catalog Number
4-PLEX adapter plates for 1- and 2-gang (4-PLEX mount directly to 4" (101.6) square device boxes).	Blue	<b>HBL4APBL</b>
	Ivory	<b>HBL4API</b>
4-PLEX APR	Red	<b>HBL4APR</b>
4-PLEX portable box. Portable 4" (101.6) square box with one cord grip. Accepts up to .66" (16.8) dia. cord.	Ivory	<b>HBL4PBI</b>

Note: 4-PLEX box is not UL Listed.

## Wallplates (Sold Separately)

Configuration	High-Impact Thermoplastic			Plated Steel	Stainless Steel (S/S) Brass		
	Color	Standard	Mid-Size				
 1-Gang	Blue	—	<b>PJ26BL</b>	Chrome Brass Plated	<b>SCH26</b> <b>SBP26</b>	Smooth S/S	<b>SS26</b>
	Gray	<b>P26GY</b>	<b>PJ26GY</b>			Smooth S/S	<b>SSJ26</b> ▲
	Ivory	<b>P26I</b>	<b>PJ26I</b>			Smooth	<b>SB26</b>
	Ivory	—	<b>PJ26C*</b>			Brass	
	Orange	<b>P26OIG**</b>	—				
	Red	<b>P26R</b>	<b>PJ26R</b>				
	White	<b>P26W</b>	<b>PJ26W</b>				

Note: \*Premarked "COMPUTER ONLY." Lettering is block 1/4" high.  
 \*\*Premarked "ISOLATED GROUND." Lettering is block 1/4" high.  
 ▲ Jumbo size plate.  
 See section O for additional wallplates.



Dimensions in Inches (mm)