


S.NO	ITEM NUMBER	CATALOG NUMBER	L	REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
				C	11/21/2017	NOTE #1 UPDATED	48086	PB	RG
1	50078948	BD12N2U	12 [305]						
2	50078949	BD18N2U	18 [457]						
3	50078950	BD24N2U	24 [610]						
4	50078951	BD36N2U	36 [914]						



NOTES:

1. APPROXIMATE AMP RATING: 190 INDOOR, 225 OUTDOOR  
CURRENTS PROVIDED ARE BASED ON A 30°C RISE OVER AMBIENT TEMPERATURE  
THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION  
OF THE BRAID AND OTHER SERVICE CONDITIONS.
2. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE  
NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
- 3> ALL SIZES ARE LISTED TO GROUNDING & BONDING EQUIPMENT STANDARDS.
- 4> BRAID SIZE MAY BE DESIGNATED BY SUFFIXES REPRESENTING VARIATIONS IN LENGTH,  
QUANTITY & SIZE OF MOUNTING HOLES, PAD SIZE AND FINISH. (REF. NOTES 3)
- 5> ADD "TN" SUFFIX FOR TIN-PLATED FERRULES.

TO ORDER BURNDY® PRODUCTS CALL				BRAID			
UNITED STATES				ITEM NO: --			
1-800-346-4175 (LONDONDERRY, NH)				CAT. NO:BD--N2U (SEE TABLE)			
CANADA:				DRAWN BY: T.SATHISH 12/19/2016			
1-800-361-6975 (QUEBEC)				CHECKER: L.TROMBLEY 1/24/2017			
1-800-387-6487 (ALL OTHER PROVINCES)				DSN APRVL: L.TROMBLEY 1/24/2017			
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>				MFG APRVL: M.STEVENS 1/18/2017			
				QA APRVL: C.LINDQUIST 1/27/2017			
				MKT APRVL: K.ROBICHEAU 2/6/2017			
				PROD FAM: --			
				PROJECT #: --			
				DOCUMENT TYPE: SALES			
				REL LEVEL: Released			
				DRAWING NO			
				50078953			
				SHEET 1 OF 1			
				REV			
				C			