CATALOG NUMBER	DESCRIPTION	CHARGER CATALOG NO.
PATCUT245-LI	PATRIOT® 245 CUTTER WITH 120V CHARGER	PATCHGRLI
PATCUT245-LIDC	PATRIOT® 245 CUTTER WITH 12V CHARGER	PATCHGRLIDC

## SPECIFICATIONS:

TOOL WEIGHT WITH BATTERY: 10.2 LBS (4.6 kg)

LENGTH: 14.5 IN (36.8 cm) WIDTH: 3.5 IN (8.9 cm) HEIGHT: 13.5 IN (34.3 cm)

OPERATING VOLTAGE: 18V-DC RECHARGE TIME: 30 MINUTES

## CUTTING CAPACITY:


COPPER & ALUMINUM CABLE UP TO 2.45" O.D. (FOR COPPER AND ALUMINUM ONLY. DO NOT CUT STEEL, GROUND ROD, REBAR OR GUY WIRE)


## FEATURES AND BENEFITS

- REFINED HYDRAULIC SYSTEM FOR ULTRA PERFOMANCE, SPEED AND RELIABILITY.
- FIELD PROVEN ELECTRONICS FOR ULTIMATE RELIABILITY IN THE HARSHEST ENVIRONMENTS.
- OVERMOLDED HANDLE FOR COMFORT AND IMPROVED GRIP; ALLOWS FOR ONE HANDED OPERATION FOR ADVANCE RETRACT AND HOLD
- SPECIALIZED LATCH HEAD DESIGN FOR INTERFERENCE FREE CLOSURE FOR MID-SPAN CUTS.
- MAKITA 18 VOLT LITHIUM-ION BATTERIES PROVIDE 2.5 TIMES MORE CHARGE/DISCHARGE CYCLES THAN TRADITIONAL NI-Cd BATTERIES AND PROVIDE 430% MORE LIFETIME WORK.
- MAKITA 30 MINUTE CHARGER CONTROLS CURRENT, VOLTAGE AMD TEMPERATURE TO MAXIMIZE BATTERY LIFE.
- FORCED AIR COOLING FAN COOLS THE BATTERY BY FORCING COOL AIR THROUGH THE BATTERY'S BUILT IN AIR VENTS.
- 180° HEAD ROTATION ALLOWS USER TO GET INTO TIGHT AREAS EASIER.
- ERGONOMICALLY BALANCED TOOL DESIGN EASES OPERATION AND LESSENS FATIGUE.
- DURABLE HIGH IMPACT FORMED CARRYING CASE PROVIDES SUPERIOR PROTECTION AND STORES ALL ACCESSORIES.
- MECHANICAL RAM RELEASE: PROVIDES CONSISTENT, RELIABLE RAM RETRACTION (NO BATTERY POWER CONSUMPTION)
- 5 YEAR LIMITED WARRANTY ON THE TOOL (EXCLUDING BLADES).
- LIFFTIME WARRANTY ON INFINITY DRIVE
- 3 YEAR LIMITED WARRANTY ON THE BATTERIES AND CHARGER.

## NOTES:

READ AND FOLLOW ALL INSTRUCTIONS PROVIDED BY THE OPERATORS MANUAL, AND WARNING LABELS BEFORE USING THIS TOOL.





- 2. TOOL ACCEPTS 18V MAKITHA LITHIUM ION BATTERIES, BL SERIES OF SIZE 2.0 AHR AND GREATER IF THE PLASTIC BATTERY CLIP IN THE TOOL HAS A "STAR" MOLDED INTO IT. THE "STAR" IDENTIFIES ACCEPTANCE OF THE BL SERIES BATTERIES.
- 3. FOR TOOLS WHICH DO NOT HAVE A "STAR" MOLDED INTO THE PLASTIC BATTERY CLIP, USE IS LIMITED TO THE BLI830 (3.0 AHR) BATTERY. FORCING ANY OTHER BATTERY INTO THIS TOOL WILL VOID THE WARRANTY.



	_			
TO ODDED BUDNEY® DEODUCTO OALL	PATRIOT® BATTERY CUTTER TOOL			
TO ORDER BURNDY® PRODUCTS CALL	ITEM NO: 30002010			
UNITED STATES:	CAT. NO: PATCUT245-LI			
	DRAWN BY: T. FAUCHER 06/30/2010			
I-800-346-4175 (LONDONDERRY, NH)	CHECKER: M. CHIASSON 10/26/2010	~ ~~~		
	DSN APPVL: M. CHIASSON 10/26/2010	e Burni		
CANADA:	MFG APPVL: S. GONYAW 10/26/2010			
I-800-36I-6975 (QUEBEC)	QA APPVL: J. BRODEUR 10/27/2010			
1-800-387-6487 (ALL OTHER PROVINCES)	MKT APPVL: R. POIRIER 10/28/2010	SCALE	: 1:4	
1-000-301-0401 (ALL OTHER PROVINCES)	PROD FAM: TOOLS, BATTERY	DRAWING NO	REV	
	PROJECT #: 14074 SIZE	30002012	1	
FOR PRODUCT INFO: http://www.burndy.com	DOCUMENT TYPE: Sales	30002012	)	
,	REL LEVEL: Released	SHEET I OF I		
·				