




## Double Arming Bolts

CATALOGUE #	DIMENSIONS	STD. PKG.	WT. LB/C	CATALOGUE #	DIMENSIONS	STD. PKG.	WT. LB/C
1458DA	5/8" x 14"	25	150	1434DA	3/4" x 14"	25	250
1658DA	5/8" x 16"	25	165	1634DA	3/4" x 16"	25	270
1858DA	5/8" x 18"	25	180	1834DA	3/4" x 18"	25	290
2058DA	5/8" x 20"	25	195	2034DA	3/4" x 20"	25	310
2258DA	5/8" x 22"	25	210	2234DA	3/4" x 22"	25	330
2458DA	5/8" x 24"	25	225	2434DA	3/4" x 24"	25	350



## Lag Bolts

CATALOGUE #	DIMENSIONS	STD. PKG.	WT. LB/C	CATALOGUE #	DIMENSIONS	STD. PKG.	WT. LB/C
2514LG	1/4" x 2 1/2"	100	4	312LG	1/2" x 3"	50	19
356LG	5/16" x 3"	100	7	412LG	1/2" x 4"	50	25
2538LG	3/8" x 2 1/2"	50	10	512LG	1/2" x 5"	50	30
338LG	3/8" x 3"	50	11	612LG	1/2" x 6"	50	35
438LG	3/8" x 4"	50	14	458LG	5/8" x 4"	25	38
4538LG	3/8" x 4 1/2"	50	15	558LG	5/8" x 5"	25	46
638LG	3/8" x 6"	50	18	658LG	5/8" x 6"	25	54



## Guy Wire

CATALOGUE #	DIAMETER	GRADE & BREAKING STRENGTH LBS.				WT. LBS/C FT.	WT. LBS/C MTRS.
		50	110	160	180		
14GW	1/4"	1,800	3,950	5,750	6,450	12.9	42.31
516GW	5/16"	3,100	6,800	9,900	11,150	22.2	72.82
38GW	3/8"	3,750	8,250	12,000	13,500	27.0	88.56
716GW	7/16"	5,410	11,900	17,300	19,500	38.8	127.26
12GW	1/2"	7,100	15,600	22,700	25,500	51.0	167.28

### Standard Coil and Spool Sizes Carried in Stock:

Spools: 5,000 ft. (1525 mtrs.); 2,500 ft. (762.5 mtrs.)

Coils: 500 ft. (152.5 mtrs.); 250 ft. (76.25 mtrs.) 100 ft.

When ordering, order by Cat No., length and grade. Please also specify *spool* or *coil*.

Prices vary only with diameter and grade, not with the size of the spool or coil.

Other grades, coils and diameters available on request.

A cutting charge applies to all special size spools and coils.

