
IN BOX® Floor Box Kit for Existing Floors

Recessed Wiring Device • Low Voltage Ports, Listed Receptacle





1 With a hole saw cut a 5" diameter hole through flooring and subfloor.



2 Use cover plate screws to secure box to floor flange assembly. Install low voltage devices into pre-installed LV keystone holder.



3 Install low voltage tie-off brackets to back of box (screws supplied). If desired, use cable ties to attach low voltage cables.



4 Place floor box into hole. Orient as desired. Tighten wing screws to secure box to floor.



CATALOG NUMBER	UPC/DEI/NAED MFG. #018997	DESCRIPTION RECESSED FLOOR BOX _FLBR5420	FINISH PLATED	UNIT/STD PKG
FLBR5420M	B 21191	Plated zinc cover, steel flange	Brass	1
FLBR5420N	L 21192	Plated zinc cover, steel flange	Nickel	1
FLBR5420Al	B 21269	Plated zinc cover, steel flange	Antique bronze	1

NUMBER	MFG. #018997	RECESSED FLOOR BOX_FLBR5420	POWDER CTD	PKG
FLBR5420BL	21266	Powder coated zinc cover, steel flange	Black	1
FLBR5420BR	21267	Powder coated zinc cover, steel flange	Brown	1
FLBR5420LA	21268	Powder coated zinc cover, steel flange	Lt Almond	1

Add suffix "GC" to catalog number when ordering for use in Canada (i.e.FLBR5420MBGC)

Kits include 24.5 cu. inch non-metallic recessed box, cULus Listed, black tamper resistant 20A decorator-style receptacle, (2) installed low voltage keystone holder inserts, (2) blank inserts, blank cover w/ gasket, in-use slotted plug cover, (3) #8 x 5/8" flat head screws, (1) NM cable connector, (2) low voltage tie-off brackets, (2) #8 x 1/2" sheet metal screws

Arlington's FLBR5420 series Recessed Floor Box Kits offer great features, like two low voltage openings, an ultra-thin stamped steel flange, and flush-to-the-floor in-use and blank covers.





Here's the solution for cost-savings and easy installation of a receptacle and low voltage connections in an existing, hard surface floor.

Because the flange is ultra thin and the wiring device is recessed these floor boxes reduce the trip hazard caused by plugs protruding from the box.

You can have power and TWO low voltage openings, in the same box, without the need for a divider. That's convenience!

Installation is quick and easy with a 5" hole saw. Four mounting wing screws attach the 24.5 cubic inch box securely to the floor.

- cULus Listed 20A tamper-resistant decorator-style receptacle.
- SIX Cover finishes/colors Metal in brass-plated, nickel-plated and antique bronze-plated zinc. And **powder-coated** in black, brown and light almond.









Patented • Made in USA