



**This item includes:**



**Item No.: 2773-500** **2**  
 Mounting carrier; for single- and double-row con.; 2773 Series; for DIN-35 rail mounting/screw mounting; orange



**Item No.: 2773-402**  
 COMPACT splicing connector; for solid and stranded conductors; max. 4 mm<sup>2</sup>; 2-conductor; transparent housing; white cover; Surrounding air temperature: max 85°C (T85); 4,00 mm<sup>2</sup>; transparent



**Item No.: 2773-408** **8**  
 COMPACT splicing connector; for solid and stranded conductors; max. 4 mm<sup>2</sup>; 8-conductor; transparent housing; light gray cover; Surrounding air temperature: max 85°C (T85); 4,00 mm<sup>2</sup>; transparent



**Item No.: 2773-403** **30**  
 COMPACT splicing connector; for solid and stranded conductors; max. 4 mm<sup>2</sup>; 3-conductor; transparent housing; orange cover; Surrounding air temperature: max 85°C (T85); 4,00 mm<sup>2</sup>; transparent



**Item No.: 2773-404**  
 COMPACT splicing connector; for solid and stranded conductors; max. 4 mm<sup>2</sup>; 4-conductor; transparent housing; red cover; Surrounding air temperature: max 85°C (T85); 4,00 mm<sup>2</sup>; transparent



**Item No.: 2773-405**  
 COMPACT splicing connector; for solid and stranded conductors; max. 4 mm<sup>2</sup>; 5-conductor; transparent housing; yellow cover; Surrounding air temperature: max 85°C (T85); 4,00 mm<sup>2</sup>; transparent



**Item No.: 2773-406** **10**  
 COMPACT splicing connector; for solid and stranded conductors; max. 4 mm<sup>2</sup>; 6-conductor; transparent housing; Gray cover; Surrounding air temperature: max 85°C (T85); 4,00 mm<sup>2</sup>; transparent

**Physical data**

Width	250 mm / 9.843 inches
Height	42 mm / 1.654 inches
Depth	106 mm / 4.173 inches

**Material Data**

Note (material data)	<a href="#">Information on material specifications can be found here</a>
Fire load	2.052 MJ
Weight	428.1 g

### Commercial data

ETIM 8.0	EC000446
ETIM 7.0	EC000446
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4055143950909
Customs tariff number	85369010000

### Downloads

#### Environmental Product Compliance

##### Compliance Search

Environmental Product  
Compliance 887-800



### Documentation

#### Additional Information

Technical Section

pdf  
2142.18 KB

