


Compression Splice

By Burndy
Catalog # [YS26](#)

2/0 AWG CU, Long Barrel, Internal Chamfer, Tin Plated,
UL/CSA, 90°C, Up to 35kV, BLACK Color Code, 13 Die Index



Application

Wire Splice

General

| | |
|------------------------|----------------------|
| Color Code | Black |
| Connector Type | LONG BARREL |
| Die Index | 13 |
| EU RoHS Indicator | Yes |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Long |
| Finish Type | Tin-Plated |
| Material | COPPER |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Sub Brand | HYLINK |
| Trade Name | HYLINK™ |
| Type | YS, Long Barrel |
| UPC | 781810507605 |
| UPC 12 Digit | 7818105076055 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - B Length inch | 1.45 in |
| Dimension - L Length Overall mm | 84 mm |
| Dimension - Length Overall inch | 3.30 in |
| Dimension - Strip Length inch | 1-1/2 |

Electrical Ratings

| | |
|-------------------|-------|
| Voltage - Maximum | 35000 |
| Voltage Rating | 35 kV |

Conductor Related

| | |
|-----------------------------------|----------------------|
| Conductor - Copper Str Navy Size | 125 (61) Navy |
| Conductor - Copper Str Size | 700 KCMIL;750 KCMIL |
| Conductor - Copper Str Size Range | 2/0 AWG |
| Conductor - Material | COPPER |
| Conductor Size | 2/0 AWG |
| Conductor Type | CODE |
| Wire Size | 700 KCMIL; 750 KCMIL |

Certifications and Compliance

| | |
|------------------------------------|--------------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|----|
| Carton Quantity | 10 |
| Minimum Pack Quantity | 1 |

Product Assets

[3D Models - YS26_MODEL-IGES](#)
[3D Models - YS26_MODEL-STEP](#)
[3D Models - YS26_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD007774-01](#)

