Retractable work surface receptacle
Concealed receptacle provides safe and convenient desktop power

With the variety of electronics and powered devices today, convenient power outlets in the home and office are critical. While phone chargers, laptops, appliances and other devices are typically located on work surfaces, outlets are often located underneath the work surface, along the wall or on the floor. Repeatedly accessing these outlets is an inconvenience and poses safety hazards.

The Carlon retractable work surface receptacle provides a convenient outlet right where you need it. A hole saw is included that attaches to your power drill to quickly mount the receptacle in a counter, desk or similar work surface. A 6-ft. cord connects to an existing wall or floor outlet, so no wiring is required. Simply pull up the receptacle's cover to raise the unit above the work surface and plug in a device. When not in use, push the cover down to store the receptacle below the work surface. The nonmetallic cover is black to complement most home or office decor.

Features and benefits:
- Provides easy access to a power outlet – simply pull up the receptacle to plug in a device
- 6-ft. cord plugs into an existing floor or wall outlet
- Receptacle remains hidden below work surface when not in use
- Compact design occupies minimal space both when recessed and while in use
- Rotated receptacle orientation accommodates over-sized power adapters
- Hole saw included
- cULus Listed, File Number E340129 (per UL 962A, Furniture Power Distribution Units)

Integral grip makes it easy to pull up the receptacle

Black nonmetallic cover complements most home or office décor

Unique rotated receptacle orientation accommodates oversized power adapters

Locking collar secures assembly to the surface

6-ft. standard corded plug connects to existing floor or wall outlet

Cat. No.	Description	Std. Ctn.
RWSR	Recessed pull-up receptacle, black, 6 ft. cord with three-prong plug	1

—
Communication accessories
Rectangular/Duplex adapters

OPODEC1-WH   OPODEC2-WH   OPODEC3-WH   OPODEC4-WH*

OPOD4-WH   OPODEC-XLRF-WH   OPODEC-XLRM-WH   OPODEC-VGA-WH

—
Rectangular/duplex adapters for use with standard floor box device plates

Cat. No.	Description	Std. Ctn.
OPODEC1-WH	Rectangular adapters for GFCI device plate, 1-port, keystone, white	5
OPODEC2-WH	Rectangular adapters for GFCI device plate, 2-port, keystone, white	5
OPODEC3-WH	Rectangular adapters for GFCI device plate, 3-port, keystone, white	5
OPODEC4-WH*	Rectangular adapters for GFCI device plate, 4-port, keystone, white	5
OPOD4-WH	Duplex adapter, 4-port, keystone, white	10
OPODEC-XLRF-WH	Rectangular adapters, female XLR microphone jack, solder leads, white	5
OPODEC-XLRM-WH	Rectangular adapters, male XLR microphone jack, solder leads, white	5
OPODEC-VGA-WH	Rectangular adapters, VGA connector, female-to-female, white	5

* Special installation note: When using these AV connectors with OPODEC4-WH & OPODEC6-WHrectangular adapters, only a blank insert (OPAB-WH) can
  be used in the same horizontal row. Trim the ears off one side of the Blank Insert and install prior to installing the AV connector in the row.

Keystone

Inserts

OPJDU5EL-WH

OPJU6L-WH

OPJV6C-WH

OPARCAW*

OPARCAR*

OPARCAY*

OPAS-WH*

OPAB-WH

—
Keystone inserts for data, voice and audio visual applications

Cat. No.	Description	Std. Ctn.
OPJDU5EL-WH	CAT5e data jack, keystone, white	5
OPJDU6L-WH	CAT6 data jack, keystone, white	5
OPJV6CL-WH	Phone jack, 6-conductor, keystone, white	5
OPARCAW*	RCA connector – white, recessed, keystone, female-to-female	5
OPARCAR*	RCA connector – red, recessed, keystone, female-to-female	5
OPARCAY*	RCA connector – yellow, recessed, keystone, female-to-female	5
OPAS-WH	S-Video connector, 4-Pin, recessed, keystone, female-to-female, white	5
OPAB-WH	Blank insert, keystone, white	25

* Special Installation Note: When using these AV connectors with OPODEC4-WH & OPODEC6-WH Rectangular Adapters, only a Blank Insert (OPABL-WH) can
  be used in the same horizontal row. Trim the ears off one side of the Blank Insert and install prior to installing the AV connector in the row.

—

Keystone

Data accessories

—
Keystone Category 5e Jacks

	Cat. No.	Description	Std. Ctn.
	OPJNUD	CAT5e Slim-Line UTP Jack, 568A/568B Wiring, Dual 110/Krone IDC, black	25
	OPJNUD-IV	CAT5e Slim-Line UTP Jack, 568A/568B Wiring, Dual 110/Krone IDC, ivory	25
	OPJNUDBL	CAT5e Slim-Line UTP Jack, 568A/568B Wiring, Dual 110/Krone IDC, blue	25
	OPJNUDOW	CAT5e Slim-Line UTP Jack, 568A/568B Wiring, Dual 110/Krone IDC, off white	25
	OPJNUDWH	CAT5e Slim-Line UTP Jack, 568A/568B Wiring, Dual 110/Krone IDC, white	25

—
Keystone RJ11 Voice Jacks

	Cat. No.	Description	Std. Ctn.
	OPJ6CVBK	6 Wire RJ11/RJ12 Voice Jack, black	25
	OPJ6CVIV	6 Wire RJ11/RJ12 Voice Jack, ivory	25
	OPJ6CVWH	6 Wire RJ11/RJ12 Voice Jack, white	25

—
Replacement parts & accessories for 68, 600, 640, 740 and 840 Series
1-, 2-, 3-Gang

692 **695** **695**

—
Floor plate plug inserts

Cat. No.	Size or description	Std. Ctn.
690-SC	$\frac{1}{2}$"–14" NPS thread	4
691-SC	$\frac{3}{4}$"–14" NPS thread	4
692-SC	1"–11$\frac{1}{2}$" NPS thread	4
692-AL	1"–11$\frac{1}{2}$" NPS thread	4
693-SC	1$\frac{1}{4}$"–11$\frac{1}{2}$" NPS thread	4
694	2"–20" UN thread	4
694-AL	2"–20" UN thread	4
695	$\frac{1}{2}$"–2"	4
695-AL	$\frac{1}{2}$"–2"	4
696-SC	$\frac{3}{4}$"–2"	4
697*	2$\frac{5}{8}$"–20" UN 2A thread	4
697-AL	2$\frac{5}{8}$"–20" UN 2A thread	4
698*	1$\frac{7}{16}$" for duplex P-60-DU	4
698-AL	1$\frac{7}{16}$" for duplex P-60-DU	4

* CSA Not applicable.

—
Gaskets for floor plate assemblies

Cat. No.	Description for use with:	Std. Ctn.
SP650	P-64 Series floor plate assemblies	4
SP651	P-64-DU floor plate assemblies	10

—
Seating plates for receptacles – steel

Cat. No.	Description for use with:	Std. Ctn.
640	P-64-2, P-64-1/2-2, P-64-3/4-2 floor plate assemblies	4
638	P-64-DS and P-64-DU floor plate assemblies	1

—
Tile trims

Cat. No.	Description	Std. Ctn.
600-4-FL-AL	Aluminum	4
600-4-FL	Brass	4