

RACKY BITS

COLOR CODED DRIVER BITS

It's so simple but it works.

Racky Bits are easier to use and harder to lose. If that's not enough, our genuine Robertson® RACKY BITS have hardened tips that fit better and last longer.



IMPACT BITS



MAGNETIC HEX BITS



DOUBLE ENDED BITS



PHILLIPS BITS



GENUINE ROBERTSON BITS



DOUBLE ENDED HEX BIT



Part# 72564RY

WE HAVE SQUARE DRIVE SCREWS AVAILABLE IN THE USA. THE BEST SCREW ON THE STREET.

#0 YELLOW ROBERTSON® SQUARE BIT PART#'S

Part# 70030Y - 3" Bulk Bit
Part# 70040Y - 4" Bulk Bit
Part# 70030YP1 - 3" Packaged Bit
Part# 70040YP1 - 4" Packaged Bit

#1 GREEN ROBERTSON® SQUARE BIT PART#'S

Part# 70120G - 2" Bulk Bit
Part# 70120GP1 - 2" Packaged Bit
Part# 70130G - 3" Bulk Bit
Part# 70140G - 4" Bulk Bit
Part# 70160G - 6" Bulk Bit
Part# 70130GP1 - 3" Packaged Bit
Part# 70130GP2 - 3" Packaged Bits (Qty 2)
Part# 70140GP1 - 4" Packaged Bit
Part# 70140GP2 - 4" Packaged Bits (Qty 2)
Part# 70160GP1 - 6" Packaged Bit
Part# 70160GP2 - 6" Packaged Bits (Qty 2)

#2 RED ROBERTSON® SQUARE BIT PART#'S

Part# 70220R - 2" Bulk Bit
Part# 70220RP1 - 2" Packaged Bit
Part# 70230R - 3" Bulk Bit
Part# 70240R - 4" Bulk Bit
Part# 70260R - 6" Bulk Bit
Part# 70230RP1 - 3" Packaged Bit
Part# 70230RP2 - 3" Packaged Bits (Qty 2)
Part# 70240RP1 - 4" Packaged Bit
Part# 70240RP2 - 4" Packaged Bits (Qty 2)
Part# 70260RP1 - 6" Packaged Bit
Part# 70260RP2 - 6" Packaged Bits (Qty 2)

#2 BLUE PHILLIPS BIT PART#'S

Part# 70241BL - 4" Bulk Bit
Part# 70241BL - 6" Bulk Bit
Part# 70241BLP1 - 4" Packaged Bit
Part# 70241BLP2 - 4" Packaged Bits (Qty 2)

#2 BLUE PHILLIPS BIT PART#'S (CONT)

Part# 70261BLP1 - 6" Packaged Bit
Part# 70261BLP2 - 6" Packaged Bits (Qty 2)

#3 BLACK ROBERTSON® SQUARE BIT PART#'S

Part# 70340BK - 4" Bulk Bit
Part# 70360BK - 6" Bulk Bit
Part# 70340BKP1 - 4" Packaged Bit
Part# 70360BKP1 - 6" Packaged Bit -

#4 ORANGE ROBERTSON® SQUARE BIT PART#

Part# 70430P

1/4" RED HEX BIT PART#'S

Part# 70531R - 2.5" Bulk Hex Bit
Part# 70561R - 6" Bulk Hex Bit
Part# 70531RP1 - 2.5" Packaged Hex Bit
Part# 70561RP1 - 6" Packaged Hex Bit

5/16" YELLOW HEX BIT PART#'S

Part# 70631Y - 2.5" Bulk Hex Bit
Part# 70661Y - 6" Bulk Hex Bit
Part# 70631YP1 - 2.5" Packaged Hex Bit
Part# 70661YP1 - 6" Packaged Hex Bit

3/8" BLUE HEX BITS PART#'S

Part# 70731BL - 2.5" Bulk Hex Bit
Part# 70761BL - 6" Bulk Hex Bit
Part# 70731BLP1 - 2.5" Packaged Hex Bit
Part# 70761BLP1 - 6" Packaged Hex Bit

7/16" BROWN HEX BIT PART#'S

Part# 70831BR - 2.5" Bulk Hex Bit
Part# 70861BR - 6" Bulk Hex Bit
Part# 70831BRP1 - 2.5" Packaged Hex Bit
Part# 70861BRP1 - 6" Packaged Hex Bit

1/2" BLACK HEX BIT PART#'S

Part# 70931BK - 2.5" Bulk Hex Bit
Part# 70961BK - 6" Bulk Hex Bit
Part# 70931BKP1 - 2.5" Packaged Hex Bit
Part# 70961BKP1 - 6" Packaged Hex Bit

DOUBLE HEX BIT PART#

Part# 72564RY - 5/16" & 1/4" Hex Bit
Part# 72564RYP1 - 5/16" & 1/4" Hex Bit Packaged

#1 & #2 DOUBLE ENDED SQUARE BIT PART#'S

Part# 72124GR - 4" Bulk Bit
Part# 72126GR - 6" Bulk Bit
Part# 72124GRP1 - 4" Packaged Bit
Part# 72124GRP2 - 4" Packaged Bits (Qty 2)
Part# 72126GRP1 - 6" Packaged Bit
Part# 72126GRP2 - 6" Packaged Bits (Qty 2)

#2 PHILLIPS & 1/4" SLOT DOUBLE ENDED BIT PART#'S

Part# 72204BY - 4" Bulk Bit
Part# 72204BYP1 - 4" Packaged Bit

#1 LIGHT BLUE PHILLIPS BIT PART#'S

Part# 70141LB - 4" Bulk Bit
Part# 70141LBP1 - 4" Packaged Bit
Part# 70141LBP2 - 4" Packaged Bits (Qty 2)

IMPACT DRIVER BITS PART#'S

Part# 7011PI - Impact Driver Bit - Phillips #1 x 1"
Part# 7012PI - Impact Driver Bit - Phillips #1 x 2"
Part# 7011RI - Impact Driver Bit - Square Green #1x1"
Part# 7012RI - Impact Driver Bit - Square Green #1 x 2"
Part# 7021PI - Impact Driver Bit - Phillips #2 x 1"
Part# 7022PI - Impact Driver Bit - Phillips #2 x 2"
Part# 7021RI - Impact Driver Bit - Square Red #2 x 1"
Part# 7022RI - Impact Driver Bit - Square Red #2 x 2"
Part# 7031RI - Impact Driver Bit - Square Black #3 x 1"
Part# 7032RI - Impact Driver Bit - Square Black #3 x 2"

RACKY BITS COUNTERTOP DISPLAY

ATTENTION WHOLESALERS!

Add a Racky Bits Acrylic Display Kit to your counter and watch the sales soar. Color-coded driver bits enable the contractor to quickly identify tip-styles and find their bits faster. Once a contractor experiences the quality and efficiency of Racky Bits, they will never want to buy another generic unpainted bit again.


Part# 70SKE12 - Empty 12-slot plexi-glass display
Part# 70SK1 - 35 bits + plexi-glass display
Part# 70SK2 - 51 bits + plexi-glass display



lockHARD bit

The lockHard bit has two strategically placed wings on the sides of its square bit end. This allows it to lock into place and makes sure you NEVER strip another screw

PART#
72133P - 3" BULK BIT
72134P - 4" BULK BIT





PANEL BUDDY

Knockout System

Tired of trying to remove knockouts? Let the Panel Buddy take care of them for you. This simple but genius tool removes knockouts in half the time, with half the effort.



FEATURES

- Kit removes knockouts on Electrical, Security, Alarm, and Datacom Panels
- Works with lipped and non-lipped panels

Part# 7WBK100

PICQUIC

Roberston



SIXPAC plus

- 7 - 3" LENGTH, 1/4" HEX POWERBITS
- 11.5" TOTAL LENGTH
- PART# P88001



GREEN ROBBY

- #5-6-7 SQUARE DRIVE
- PART# SD110G



DASH 7

- 7 - 2" LENGTH, 1/4" HEX POWERBITS
- COMES IN 4 BRIGHT NEW COLORS
- PART# P05001



RED ROBBY

- #8-9-10 SQUARE DRIVE
- PART# SD210R



STUBBY

- SOLID, COMFORTABLE, HIGH TORQUE HANDLE
- 6 HIGH QUALITY 1.3" LENGTH INSERT BITS
- IDEAL FOR WORK IN CLOSE QUARTERS
- PART# P91000



BLACK ROBBY

- #12-13-14 SQUARE DRIVE
- PART# SD310BK



DEMAGNETIZER

MAGNETIZES OR DEMAGNETIZES DRIVER BITS, TOOLS AND SMALL STEEL PARTS INSTANTLY!
Part# 70988

MAGNETIC BIT HOLDER

QUICK CHANGE MAGNETIC BIT HOLDER
PART# 72000

- WORKS ON JAGGED, UNEVEN AND ROUGH BREAKS
- SELF CENTERING TIP, NO WALKING
- COMPATIBLE WITH QUICK CONNECT CHUCK SYSTEMS
- EASY TO USE WITH 3/8" VARIABLE SPEED REVERSIBLE DRILL
- EXTRACTS SCREWS UP TO 4 INCHES



proGrabit

DAMAGED SCREW REMOVER


PART# 72120

ROLGEAR

MULTIBIT RATCHET SCREWDRIVER / 15 TIPS (DOUBLE ENDED BITS)

- Slotted: 3/16", 1/4"
- Square: 1, 2, 3, 4
- Phillips: 1, 2, 3, 4
- Torx: 10, 15, 20, 25
- Smooth and silent ratcheting
- Single-handed ratchet adjustments from forward, locked, & backward
- Ergonomic, cushion comfort handle
- Magnetic components for drop-safe bit changing
- Stainless steel bit adapter

PART# SDR14



HOLDSABIT

Every moment during a project that you spend looking for the right tool is wasted time and results in frustration and bad decisions. The ingenious HOLDSaBIT slips on or off a drill in seconds. Simply pull one loop over the front of the drill and pull the second loop to the back of the drill. The HOLDSaBIT will hold any 1/4" hex shank item as well as pencils, nut drivers and hex shank drill bits. Tips and bits are easily inserted and removed.



FEATURES:

- Sold in a kit with bits or sold separately.
- Hold any 1/4" hex shank items as well as pencils, drill bits, etc.
- 4 channels to fit a variety of length bits



Part# 70000 (Bits Not Included)

Part# 700.kit (includes 1-70140G, 1-70240R, 1-70241BL, 1-70531R, 1-70631Y & 1-72133P)

REVBIT: REVERSE PILOT BIT

The RevBit takes a common item, the pilot bit, and perfects it. By being reverse twist the RevBit eliminates any bending, breaking and mess caused by hole saw teeth catching once your pilot bit goes through the material.

FEATURES:

- Reverse threaded pilot bit for a soft landing once the pilot bit breaches the work surface
- 4" in length
- Made from high speed steel
- Works with any standard hole saw
- Will not tear sheetrock, or finished wall surface
- Preserves the hole saw teeth, for the entire life of the tool
- Made in the USA



Part# 91700



NUT BLASTER

Univeral Wire Connector

- Fast, easy installation
- Prevents sore fingers and cramping hands
- Available in two sizes

Part#

XL - 72101 - Fits all brands yellow, tan

& red twist on wire connectors

XXL - 72102 - Fits all brands large grey

& blue twist on wire connectors




NUT BLASTER

In-Store Display

Contact us to order this counter display. Other counter displays also available.

THE TOP HAT



 PART# TC1400
 *PACKAGED IN 50 & 5 PACKS



As a simple box cover, the Top Hat is used instead of a blank cover with several important advantages. It allows installers to leave wires that enter the junction boxes extending straight. With the depth of the Top Hat there is no need to coil wires and stuff them into the smaller parts of the junction box. This will save time during installation and more importantly during troubleshooting. Additionally, this high volume cover makes it easier to access the contents of any junction box.

FEATURES

- ULC Approved
- Adds 35.8 cubic inches to the existing junction box
- Plenum Rated
- Patent Pending



BEFORE



AFTER

6.5 INCH PLATE

FEATURES:

- Installs in seconds with rare earth magnets - snaps in place to metal clips (included)
- White decorative plate covers and 5-1/2" square hole or electrical box
- Can also be used to cover a round hole with up to a 5-1/2" diameter
- Visually appealing white decorative plate - no need to paint metal covers



Part# D612

SC500 - Aircraft Seismic Cable 500'
 SC1000 - Aircraft Seismic Cable 1000'
 SCC116 - Aircraft Seismic Cable Clamps



AIRCRAFT CABLE & WIRE CRIMPS

- AVAILABLE IN 500 AND 1,000 FEET.
- NO NEED TO GO ANYWHERE ELSE - BUY IT FROM US!

BOLT STAR® POLE POSITIONING TOOL

INTRODUCING BOLT STAR®
 An innovative, multi-function reusable bolt template engineered to hold four anchor bolts, rebar cage and conduits securely in place during the pour of a concrete pole base. The result of years of design refinement and testing, BOLT STAR radically improves the productivity of crews in the construction of light pole bases and round column forms. Available for 180 and 240 tube sizes, the tool virtually eliminates the drawbacks of wood templates.



SAVES LABOR - REUSABLE - REDUCES RISK

- Part# 67218 - Small Size 18" - Green
- Part# 67224 - Large Size 24" - Orange
- Part# 67230 - Extra Large Size - Yellow
- Part# 67234 - Extension Set of 4 Pcs. - Black

BOLT TEMPLATE

The Bolt Template helps you easily layout bolts to be used in concrete for future installation of poles or beams. The template is multi-functional and has an easy guide for centering bolts.



- Has a whopping 41 templates!
- Quick, easy, and reusable
- Weather resistant ABS plastic
- Sets poles and beams 8" - 24"

Part# 67441



DRYCONN® WATERPROOF CONNECTORS

FILLED CONNECTORS FOR OUTDOOR USE



FILLED CONNECTORS FOR DIRECT BURY USE

Part #	Selling Unit	Wire Range
KI62110	Card of 6	22 — 12
KI62125	Bag of 25	22 — 12
KI62210	Card of 5	22 — 8
KI62225	Bag of 20	22 — 8
KI62310	Card of 3	14 — 6
KI62335	Bag of 50	14 — 6



"One-Step"® Installations
 Corrosion Proof
 Reduces Risk of Fire
 CSA certified as a Pressure Type Connector

Part #	Selling Unit	Wire Range
KI10600	Card of 2	22 — 8
KI10666	Bag of 10	22 — 8
KI10999	Bag of 8	14 — 6
KI10444	Bag of 10	18 — 12
KI10555	Bag of 10	14 — 10

"One-Step" Installations
 CSA certified as a Pressure Type Connector
 CSA certified as Direct Bury
 Corrosion proof