

CABLE MOUNTS

The Rack-A-Tiers Saddle Support is a saddle where you put a screw through an d strap wire with tie wraps. Let's be honest, Rack-A-Tiers didn't reinvent the wheel with this one, but we did reinvent the price.

Another exciting, already available product we're adding are the 4-way adhesive cable tie mounts in 2 different sizes. You know what these are for. Buy them from us if you would like to.

Part# RC215WT


Cable Tie Saddle Support White
1.5" (100 pcs)

Part# RC4150WT

Cable Tie Mount 4-Way Adhesive White
1 1/2" (100 pcs)

Part# RC410WT

Cable Tie Mount 4-Way Adhesive White
1" (100 pcs)



CHASE STRAP CONDUIT BRACKET



The Chase Strap secures the short piece of conduit extending from one room to another through a sheetrock wall or other barrier such as a concrete riser. The strap is made from galvanized steel and is available in multiple sizes.

Part#

- RCS100 - 1" Chase Strap - 20 Per Box
- RCS200 - 2" Chase Strap - 20 Per Box
- RCS400 - 4" Chase Strap - 10 Per Box



UL Listing E507150



Winnie Industries

MANUFACTURER OF FASTENING SUPPORTS

*See Web Site For More Variations
(All sold in packs of 10)

MAGNETIC CABLE TIE MOUNTS



16 LB Magnetic
Cable Tie Mount - UV Black
Part# RMW016BK



16 LB Magnetic
Cable Tie Mount - UV Black
Part# RMW016WT

100 Lb Magnetic Mount
1/4-20 Threaded
Part# RMW1420F



26 LB Magnetic
Cable Tie Mount - White/Natural
Part# RMW026WT



26 LB Magnetic
Cable Tie Mount - UV Black
Part# RMW026BK



26LB Magnetic
1 inch wide, Grip Tape Mount
- UV Black
Part# RMW226BK

MAGNETIC BRIDLE RINGS



26 Lb Magnet
3/4" Magnetic Bridle Ring,
Small Standoff, Zinc Plated
Part# RMW075BR




100 Lb Magnet
1 1/4" Magnetic Bridle Ring,
Small Standoff
Part# RMW125BR



100 Lb Magnet
2" Magnetic Bridle Ring,
Small Standoff
Part# RMW200BR

THE X-DISPENSER

FOLDING WIRE CADDY



Part #11655

- Maximum spool quantity: 6. 500' reels of #10 AWG wire.
- Maximum spool diameter: 8".
- Max spool width: 9".
- Folds to 1" wide to easily fit in your van.
- Easy to carry: 1" by 23".

The X-Dispenser is a portable, fold-up wire dispensing device. Folds down to just 1" thick to easily fit in your work vehicle. Easy to set up, easy to put away. The X-Dispenser will become your go to wire dispenser when it comes to pulling smaller, single conductor spools.

ER-GO 50

SPOOL CARRIER



Ergonomic carrier, specially designed for the manual transportation of wire spools (electric wiring, steel cable, chain, etc.)

Maximum lifting capacity: 22.6 kg (50 lbs).
One year warranty against defects.

Made in Canada



Part# 56050

THE STICK

STUD MOUNTED WIRE DISPENSER

The Stick installs quickly & easily to any standard stud. Its compact design allows for easy storage once the job is complete.

- Weight capacity: 200 lbs.
- Maximum 15" reel width.



Part #11555

REEL-END

REUSABLE SPOOL REEL TOOL

Part# 17455

FEATURES:

- Pays for itself with the first roll saved and it's reusable
- Organize your wire spools with the reel-end wire spool repair kit
- The Reel-End repairs common plastic spools #10 through #18 gauge.
- 6 1/2" Diameter



Hooker

PIPE WRENCH ADAPTER

The Hooker Pipe Wrench Adaptor lets you turn your Rack-A-Tiers Wire Dispenser into a pipe vise.

- Light weight.
- Easy to use.
- Fast implementation.
- Inexpensive.
- To be used with an 18 rigid pipe wrench.



Part #10455