

IEC Products



DESCRIPTION						AMPERES	CATALOGUE #
-------------	--	--	--	--	--	---------	-------------

C2000 Contactors and Starters

SINGLE PHASE HP @ 60HZ		THREE PHASE HP @ 60HZ					
115V	230V	200V	230V	460V	575V		
0.5	1.5	3	3	5	7.5	10A	CL00A310TJ
0.75	2	3	3	7.5	10	13.8A	CL01A310TJ
1	3	5	5	10	15	17.5A	CL02A310TJ
1.5	3	5	7.5	15	15	22A	CL25A310TJ
2	5	10	10	20	25	32A	CL04A310MJ
3	5	10	10	25	25	34A	CL45A310MJ
3	7.5	15	15	30	40	48A	CL06A311MJ
5	10	20	20	40	50	62A	CL07A311MJ
5	15	20	25	50	60	68A	CL08A311MJ
7.5	15	25	30	60	75	80A	CL09A311MJ
10	20	30	40	75	75	96A	CL10A311MJ
0.5	1.5	3	3	5	7.5	10A	LAR00AJ
0.75	2	3	3	7.5	10	13.8A	LAR01AJ
1	3	5	5	10	15	17.5A	LAR02AJ
1.5	3	5	7.5	15	15	22A	LAR25AJ
2	5	10	10	20	25	32A	LAR04AJ
3	5	10	10	25	25	34A	LAR45AJ
3	7.5	15	15	30	40	48A	LAR06AJ
5	10	20	20	40	50	62A	LAR07AJ
5	15	20	25	50	60	68A	LAR08AJ
7.5	15	25	30	60	75	80A	LAR09AJ
10	20	30	40	75	75	96A	LAR10AJ

- Open Contactors, 3-pole Non-reversing c/w 120v coil 600v max. AC Controlled
- For larger contactors up to 602A
- Open Contactors, 3-pole Reversing c/w 120v coil 600v max. AC Controlled
- For larger contactors up to 602A

Coil replacement, AC 60Hz

24V	For use with coil suffix* C	CL00, CL01, CL02, CL25	LB1A*
48V	For use with coil suffix* F		
120V	For use with coil suffix* J	CL04, CL45	LB3A*
208V	For use with coil suffix* L		
277V	For use with coil suffix* N	CL06, CL07, CL08, CL09, CL10	LB4A*
240V	For use with coil suffix* S		
480V	For use with coil suffix* U		
600V	For use with coil suffix* Y		



www.ge-ed.ca
www.geindustrial.com
1-800-GE-1STOP