














Mercmaster™ LED Generation 3 Series Luminaires

Enclosed and Gasketed Fixtures

NEC/CEC: Class I, Division 2, Groups A, B, C, D Class II, Division 1 and 2, Group E, F, G Class III Class I, Zone 2 AEx ec IIC Zone 21 AEx tb IIIC Class I, Zone 2 Ex ec II	NEC/CEC: Zone 21 Ex tb IIIC Type 3R, 4, 4X IP66/IP67 Simultaneous Exposure Suitable for Use in Wet Locations	NEC/CEC: Marine Outside Type (Salt Water) American Bureau of Shipping (ABS) Certified International Dark Sky (IDA) Approved	ATEX: Zone 2 and 21/22 II 3 G II 2 GD IP66 IK08	IECEx: Zone 2 and 21/22 Ex ec IIC Ex tb IIIC Ex tc IIIC IP66 IK08
--	--	---	---	--

Accessories and Replacement Parts

		Description	Catalog Number
Globes			
		Clear Globe (polycarbonate)	VPGL-LED
		Diffused Globe (polycarbonate)	VPGL-DIFF
		Glass Globe	VPGL-GLASS
		Light Distribution	Catalog Number
Closed Prismatic Glass Refractors — All Heat-Resistant			
		Short Prismatic Glass Refractor NEMA Type V	LPG-R5S
Short Refractor ②	Tall Refractor ②	Tall Prismatic Glass Refractor NEMA Type V	LPG-R5
		Description	Catalog Number
Reflector			
		30° Angle White Polyester Reflectors	CMR-4AN
30° Angle			
Guards			
			
Glass Globe Guard	Short Refractor Guard	Tall Refractor Guard	
		Glass Globe Guard	MGU1
		Short Refractor Guard for LPG-R5S	KRG2S
		Tall Refractor Guard for LPG-R5	KRG2
Safety Cable			
		Stainless steel	LEDSC
Visor			
		Electrostatically applied gray epoxy powder coat finish on Aluminum Visor	MMVISOR
Mounting Hood Adapters ①			
	Manufacturer	Installed Mounting Hood	Appleton Adapter Catalog Number
	Crouse-Hinds™ Champ®	APM2/3 - Pendant CM2/3 - Ceiling HPM2 - Flexible Pendant	MMADCHVS
	Appleton™ Mercmaster™ II	LPA75/100 - Pendant LPC75/100 - Ceiling TWM2/3 - Wall	MMADIIS
	Crouse-Hinds™ Champ®	JM5 - 25° Angle Stanchion PM5 - 90° Straight Stanchion	MMADCHVA
	Appleton™ Mercmaster™ II	LPWB75, LPWB100 - Wall LPS125, LPS150 - 25° Angle Stanchion	MMADIIA
	Killark™	VMX2B, VMX3B, VMX6B, VMX7B, VMX9B - Ceiling VMA2B, VMA3B - Pendant VMD4B, VMD5B, VMS4B, VMS5B - Stanchion VMB2B, VMB3B - Wall VMC2B, VMC3B - Pendant Cone	MMADKVA

① Adapters are cCSAus rated only

② Glass Prismatic Refractor is cCSAus rated only.