

Box terminal TS1.1 3 units 14 AWG...3/0 accessories for: 3VA4/5 125



Model		
product brand name	SENTRON	
product designation	accessories	
design of the product	box terminal 3 units	
accessories	Box terminal	
General technical data		
designation / of the terminal	TS1.1	
type of electrical connection / with control wire tap	No	
Connections according IEC		
connectable conductor cross-section		
<ul style="list-style-type: none"> for copper cable / stranded / minimum 	1.5 mm ²	
<ul style="list-style-type: none"> for copper cable / stranded / maximum 	70 mm ²	
stripped length	12 mm	
tightening torque / when using copper cables		
<ul style="list-style-type: none"> solid 	1.5 - 16 mm ² : 45 lb-in	
<ul style="list-style-type: none"> stranded 	1.5 - 16 mm ² : 45 lb-in 25 - 70 mm ² : 70 lb-in	
<ul style="list-style-type: none"> finely stranded 	1.5 - 16 mm ² : 45 lb-in 25 - 50 mm ² : 70 lb-in	
Connections according UL		
stripped length	0.5 in	
connectable conductor cross-section		
<ul style="list-style-type: none"> for copper cable / solid / minimum 	14 AWG	
<ul style="list-style-type: none"> for copper cable / solid / maximum 	10 AWG	
<ul style="list-style-type: none"> for copper cable / stranded / minimum 	14 AWG	
<ul style="list-style-type: none"> for copper cable / stranded / maximum 	3/0 AWG	
<ul style="list-style-type: none"> for copper cable / finely stranded / minimum 	14 AWG	
<ul style="list-style-type: none"> for copper cable / finely stranded / maximum 	3/0 AWG	
tightening torque / when using copper cables		
<ul style="list-style-type: none"> solid 	14 - 10 AWG: 45 lb-in	
<ul style="list-style-type: none"> stranded 	14 - 6 AWG: 45 lb-in 4 AWG - 3/0: 70 lb-in	
<ul style="list-style-type: none"> finely stranded 	14 - 6 AWG: 45 lb-in 4 AWG - 3/0: 70 lb-in	
Certificates		
General Product Approval	EMC	Declaration of Conformity



[Miscellaneous](#)



Marine / Shipping

other

Environment

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9133-0JA11>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9133-0JA11>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9133-0JA11

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

8/17/2022

