



Label holder, 22mm, flat, Frame rounded off at the bottom black, for labeling plate 12.5 mm x 27 mm, for gluing

|   |                                 |
|---|---------------------------------|
| product brand name  | SIRIUS ACT                      |
| product designation   | Label holder                    |
| design of the product   | for labeling plate 12.5 x 27 mm |
| product type designation  | 3SU1                            |
| <b>General technical data</b>                                       |                                 |
| protection class IP   | IP66, IP67, IP69(IP69K)         |
| degree of protection NEMA rating                                    | 1, 2, 3, 3R, 4, 4X, 12          |
| shock resistance for railway applications according to EN 61373     | Category 1, Class B             |
| vibration resistance for railway applications according to EN 61373 | Category 1, Class B             |
| Substance Prohibitance (Date)                                       | 10/01/2014                      |
| <b>Ambient conditions</b>   |                                 |
| ambient temperature   |                                 |
| • during operation  | 70 ... -25 °C                   |
| • during storage and transport                                      | 80 ... -40 °C                   |
| <b>Installation/ mounting/ dimensions</b>                           |                                 |
| height  | 44.8 mm                         |
| width   | 29.8 mm                         |
| <b>Accessories</b>  |                                 |
| material of accessory   | Plastic                         |
| shape of label holder   | rounded below                   |
| color of label holder   | Black                           |
| fastening method of label   | stick                           |
| <b>Certificates/ approvals</b>                                      |                                 |
| General Product Approval  | Declaration of Conformity       |



[Confirmation](#)



|                   |                   |       |
|-------------------|-------------------|-------|
| Test Certificates | Marine / Shipping | other |
|-------------------|-------------------|-------|

[Type Test Certificates/Test Report](#)



[Confirmation](#)

**Environment**

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1900-0AG10-0AA0>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1900-0AG10-0AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1900-0AG10-0AA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1900-0AG10-0AA0&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1900-0AG10-0AA0&lang=en)



last modified:

3/29/2022