

TRAC-LITES 120V PAR16/MR16 GU10 SERIES

Project: Fixture Type: Location: Contact/Phone:

R711, R712, R714, R715 **R717** and **R718**

PRODUCT DESCRIPTION

Lampholder Ceramic base twist-and-lock GU10 socket with nickel plated contacts.

Aiming 90° vertical aiming capability and 358° rotation.

Adapter Copper alloy contacts provide precise spring action • True, positive electrical ground • On/off switch included • Patented embossed polarity arrows on bottom of adapter • Spring-loaded locking latch with embossed polarity arrows secures track light to track • Compatible with both Trac-Lites and Trac-Master track • "Pull-up" contact to up position for use on Trac-Master two-circuit track.

Labels UL/CUL listed.

Note: Actual performance may differ as a result of end-user environment and application. Specifications subject to change without notice.














Line Voltage GU10 Open Back Spotlight

Construction Drawn steel housing with die-formed steel yoke.


Catalog Number	Finish	Lamp
R711 WH	White	120V, 35-50W PAR16/MR16 GU10
R711 BL	Black	120V, 35-50W PAR16/MR16 GU10



Line Voltage GU10 Round Back Cylinder

Construction Drawn steel housing with die-formed steel yoke.


Catalog Number	Finish	Lamp
R712 BL	Black with Black Bezel	120V, 35-50W PAR16/MR16 GU10



Line Voltage GU10 Cast Cube

Construction Drawn steel housing with die-formed steel yoke.

Catalog Number	Finish	Lamp
R714 WH	White	120V, 35-50W PAR16/MR16 GU10
R714 BL	Black	120V, 35-50W PAR16/MR16 GU10
R714 SC	Satin Chrome	120V, 35-50W PAR16/MR16 GU10
R714 BZ	Painted Bronze	120V, 35-50W PAR16/MR16 GU10




TRAC-LITES 120V PAR16/MR16 GU10 SERIES

R711, R712, R714, R715 **R717** and **R718**

Line Voltage GU10 Flare

Construction Drawn steel housing with machined steel stem.


Catalog Number	Finish	Lamp
R715 WH	White	120V, 35-50W PAR16/MR16 GU10
R715 BL	Black	120V, 35-50W PAR16/MR16 GU10
R715 SC	Satin Chrome	120V, 35-50W PAR16/MR16 GU10
R715 BZ	Painted Bronze	120V, 35-50W PAR16/MR16 GU10



Line Voltage GU10 Odyssey

Construction Die cast aluminum hosing with machined steel stem.

Catalog Number	Finish	Lamp
R717 WH	White	120V, 35-50W PAR16/MR16 GU10
R717 SC	Satin Chrome	120V, 35-50W PAR16/MR16 GU10



Line Voltage GU10 Bell

Construction Die cast aluminum housing and swivel arm • Deep lamp regression and spun aluminum step baffle to reduce glare.

Catalog Number	Finish	Lamp
R718 BZ	Oil Bronze	120V, 35-50W PAR16/MR16 GU10

