



Trac-Master™ Classics Series

Timeless track lighting solutions

JUNO®



Trac-Master™ Classics - Stylish Familiarity

Juno Classics are benchmark fixture designs that incorporate timeless shapes and themes. These simple yet elegant fixtures provide economical track lighting solutions in extremely practical, functional packages. Comprised mainly of gimbal rings, cylinders, and universals, Juno design Classics are offered in a variety

of finishes to suit most any décor. Familiar lines and traditional shapes create levels of visual comfort typically not encountered in more contemporary styles. Primarily designed for PAR and R/BR lamps, these uncomplicated fixture styles offer unpretentious aesthetics that blend well in any environment.



Open Back Gimbals

Gimbal rings are ever popular due to their long-standing use as an economical, general-purpose trac lampholder.

Finishes

White (WH) Black (BL) Natural (NAT) Satin Chrome (SC)

Series	Lamp	Dimensions
T362	35-50W PAR20	

Finishes: WH, BL

Series	Lamp	Dimensions
T363	35-75W PAR30	

Finishes: WH, BL, SC, NAT

Series	Lamp	Dimensions
T368	45-150W PAR38	

See specification sheet for optional accessories.

Finishes: WH, BL, SC*, NAT

Front Lamping Gimbals

A Juno innovation, the front-loading gimbal-ring combines the practicality, versatility and economy of traditional gimbal ring trac fixtures with a fixed front ring to allow simplified front relamping.

Finishes

White (WH) Black (BL) Natural (NAT) Silver (SL)

Series	Lamp	Dimensions
T687	35-50W PAR20	

Finishes: WH, BL, NAT*, SL*

Series	Lamp	Dimensions
T689	35-50W PAR30	

Finishes: WH, BL, NAT, SL*

Series	Lamp	Dimensions
T690	35-250W PAR38	

Finishes: WH, BL, NAT, SL

Note: The Natural (NAT) finish is merely a raw finish with a clear protective coating applied - Inconsistencies, scratches, and minor processing marks are part of the unique aesthetic created by this process and should be expected.

*Limited quantities remain - consult factory.



Universals

The economical, universal lampholders accept a wide range of wattages and sizes of popular halogen PAR and incandescent R/BR lamps.

Finishes

White (WH)
 Black (BL)
 Natural (NAT)

Series	Lamp	Dimensions
T301	30-50W R20/35-50W PAR20/ 45-85W BR30/35-75W PAR30/ 65-120W BR40/45-150W PAR38	

Finishes: WH, BL

Series	Lamp	Dimensions
T620	30-50W R20/35-50W PAR20/ 45-85W BR30/35-75W PAR30/ 65-120W BR40/45-150W PAR38	

Finishes: WH, BL

Series	Lamp	Dimensions
T308	30-50W R20/35-50W PAR20/ 45-85W BR30/35-75W PAR30/ 65-120W BR40/45-150W PAR38	

Finishes: WH, BL

Series	Lamp	Dimensions
T691	45-60W PAR16/35-50W PAR20/ 35-75W PAR30/45-150W PAR38	

Finishes: WH, BL, NAT

Series	Lamp	Dimensions
T359	30-50W R20/35-50W PAR20/ 45-85W BR30/35-75W PAR30/ 65-120W BR40/45-150W PAR38	

Finishes: WH

Accessories for T308 and T620		Dimensions
T63	65W BR30/75W PAR30 Baffled hood with black baffle for T620	
Finishes: WHT, BLCK		

T64	120W BR40/150W PAR38 Baffled hood with black baffle for T620	
Finishes: BLCK*		

Note: The Natural (NAT) finish is merely a raw finish with a clear protective coating applied - inconsistencies, scratches, and minor processing marks are part of the unique aesthetic created by this process and should be expected.

*Limited quantities remain - consult factory.



T420



T421



T423



T425



T427

Mini-PARs

Most cylindrical track fixtures pre-date the availability of halogen PAR lamps and are typically sized for the longer incandescent reflector lamps. On the contrary, Juno Mini-PARs are optimized around the shorter dimensions of halogen PAR lamps, thus offering a more contemporary, compact appearance.

Finishes

White (WH) Black (BL)** Satin Chrome (SC)

** Black finish lampholders are supplied with both black and red adjusting buttons.

Round Back

Series	Lamp	Baffle Color	Dimensions
T420 WHB T420 BLB	45-60W PAR16	White Baffle Black Baffle	

Finishes: T420 WHB: WH; T420 BLB: WH, BL, SC*

Flat Back

Series	Lamp	Baffle Color	Dimensions
T425 WHB T425 BLB	35-75W PAR30	White Baffle Black Baffle	

See specification sheet for optional accessories.

Finishes: T425 WHB: WH; T425 BLB: WH*, BL

Flat Back

Series	Lamp	Baffle Color	Dimensions
T421 WHB T421 BLB	45-60W PAR16	White Baffle Black Baffle	

Finishes: T421 WHB: WH; T421 BLB: WH*, BL

Series	Lamp	Baffle Color	Dimensions
T427 BLB	45-250W PAR38	Black Baffle	

See specification sheet for optional accessories.

Finishes: BL

Series	Lamp	Baffle Color	Dimensions
T423 WHB T423 BLB	35-50W PAR20	White Baffle Black Baffle	

See specification sheet for optional accessories.

Finishes: T423 WHB: WH; T423 BLB: WH*, BL, SC

*Limited quantities remain - consult factory.



T366



T371



T372

Halogen Flood

These economical quartz halogen floodlights provide crisp, white halogen light from a very compact fixture. The integral black barn doors on the T366 provide brightness control and allow shaping of the light cut-off.

Finishes

White (WH) Black (BL)

Series	Lamp	Dimensions
T366	75-250W T4 DC BAYONET	

Finishes: WH, BL

Series	Lamp	Dimensions
T367	75-250W T4 DC BAYONET	

Finishes: WH

RLMs

These pendant and wall wash fixtures capture the ambiance of old-world industrial and loft spaces for which they were originally designed. They take advantage of economical A-lamps to produce soft, even illumination.

Finishes

White (WH)

Series	Lamp	Dimensions
T371	100W A19/150W A21	

Finishes: WH

Series	Lamp	Dimensions
T372	100W A19/150W A21	

Finishes: WH



Flat Back Cylinders

These long-standing traditional lampholders accept a wide range of both halogen PAR and incandescent R/BR lamps and provide deep lamp shielding.

Finishes

White (WH) Black (BL)

Series	Lamp	Baffle Color	Dimensions
T311 BLB	15-40W R14 or 40W R16 Intermediate Screw Base with Black Baffle	Black Baffle	

Finishes: WH, BL

Series	Lamp	Baffle Color	Dimensions
T317 WHB T317 BLB	65-120W BR40 or 45-150W PAR38	White Baffle Black Baffle	

See specification sheet for optional accessories.

Finishes: T317 WHB: WH; T317 BLB: WH, BL

Series	Lamp	Baffle Color	Dimensions
T313 WHB T313 BLB	27-50W R20	White Baffle Black Baffle	

See specification sheet for optional accessories.

Finishes: T313 WHB: WH, T313 BLB: WH*, BL

Series	Lamp	Baffle Color	Dimensions
T340	12V, 20-50W MR16	Black Baffle	

See specification sheet for optional accessories.

Finishes: WH, BL

Series	Lamp	Baffle Color	Dimensions
T315 WHB T315 BLB	35-75W BR30 or 45-75W PAR30L	White Baffle Black Baffle	

See specification sheet for optional accessories.

Finishes: T315 WHB: WH; T315 BLB: WH, BL

Series	Lamp	Baffle Color	Dimensions
T342 WHB T342 BLB	45-250W PAR38	White Baffle Black Baffle	

See specification sheet for optional accessories.

Finishes: T342 WHB: WH; T342 BLB: WH*, BL

*Limited quantities remain - consult factory.




Round Back Cylinders

The timeless round-back shape accepts a range of both halogen PAR and incandescent R/BR lamps and provides deep lamp shielding.


Finishes

White (WH) Black (BL)

Series	Lamp	Baffle Color	Dimensions
T326 WHB T326 BLB	27-50W R20	White Baffle. Black Baffle	


See specification sheet for optional accessories.

Finishes: T326 WHB: WH, T326 BLB: WH*, BL

Series	Lamp	Baffle Color	Dimensions
T327 WHB T327 BLB	45-75W BR30 or 35-75W PAR30L	White Baffle Black Baffle	

See specification sheet for optional accessories.

Finishes: T327 WHB: WH, T327 BLB: WH, BL

Series	Lamp	Baffle Color	Dimensions
T328 WHB T328 BLB	65-120W BR40 or 45-150W PAR38	White Baffle Black Baffle	

See specification sheet for optional accessories.

Finishes: T328 WHB: WH, T328 BLB: WH, BL

*Limited quantities remain - consult factory.

Photo Credits:


Cover: Crate and Barrel (Mark Steele Photography)
Inside Front Cover: Helzberg Diamonds (Mark Steele Photography)

Step Cylinders

One of the original track lampholder designs. Step Cylinders are still popular for more utilitarian applications and accept a range of both halogen PAR and incandescent R/BR lamps and provide deep lamp shielding.


Finishes

White (WH) Black (BL)

Series	Lamp	Baffle Color	Dimensions
T303 WHB T303 BLB	27-50W R20	White Baffle. Black Baffle	


See specification sheet for optional accessories.

Finishes: T303 WHB: WH, T303 BLB: WH*, BL

Series	Lamp	Baffle Color	Dimensions
T305 WHB T305 BLB	45-75W BR30 or 35-75W PAR30L	White Baffle Black Baffle	

See specification sheet for optional accessories.

Finishes: T305 WHB: WH*, T305 BLB: WH, BL

Series	Lamp	Baffle Color	Dimensions
T307 BLB	65-120W BR40 or 45-150W PAR38	Black Baffle	

See specification sheet for optional accessories.

Finishes: WH*, BL

