
















Project: _____

Fixture Type: _____

Location: _____

Contact/Phone: _____

Trim Series	Dimensions	Aperture	Catalog No.	Housing/ Lamp Compatibility
 Frosted Lens with Clear Center			12 WWH 4" Frosted Lens With Clear Center Trim - White, White Trim Ring 12 WSC 4" Frosted Lens With Clear Center Trim - Perimeter Frosted Lens, Satin Chrome Trim Ring 12 WABZ 4" Frosted Lens With Clear Center Trim - Perimeter Frosted Lens, Classic Aged Bronze Trim Ring	IC1/ IC1 W/ IC1 S: 30W R20, 50W PAR20 (Requires T599 Socket Extender) TC1RC W : 50W PAR20, APT1: 50W PAR20, 50W R20 IC1P: 50W PAR20, 50W R20, 40W K19 TC1/ TC1 S/ TC1R: 50W PAR20, 50W R20 ICPL4: 26W, 18W PL4: 26W, 18W IC1LED: G4 O6LM, WD G4N O6LM/G4 O9LM, WD G4 O9LM IC1RLED: G4 O6LM, WD G4N O6LM/G4 O9LM, WD G4 O9LM
 Drop Oval			11 WH 4" Lensed Drop Opal Trim - White	IC1/ IC1 W/ IC1 S: 30W R20, 35W PAR20 IC1P: 50W PAR20, 30W R20, 40W K19, TC1RC W: 50W PAR20 TC1/ TC1 S/ TC1R: 50W PAR20, 50W R20 ICPL4: 26W, 18W Do not use with ICPL4R 18W E PL4: 26W, 18W IC1LED: G4 O6LM, WD G4N O6LM/G4 O9LM, WD G4 O9LM IC1RLED: G4 O6LM, WD G4N O6LM/G4 O9LM, WD G4 O9LM APT1: 50W PAR20, 50W R20
 Beveled Lensed			4102 ABZ 4" Decorative Beveled Lens Trim - Classic Aged Bronze 4102 SC 4" Decorative Beveled Lens Trim - Satin Chrome 4102 WH 4" Decorative Beveled Lens Trim - White	IC1/ IC1 W/ IC1 S: 50W PAR20, 30W R20 IC1P /TC1/ TC1 S/ TC1R: 50W PAR20, 50W R20 TC1RC W : 50W PAR20, APT1: 50W PAR20, 50W R20 ICPL4: 26W, 18W PL4: 26W, 18W IC1LED: G4 O6LM, WD G4N O6LM/G4 O9LM, WD G4 O9LM IC1RLED: G4 O6LM, WD G4N O6LM/G4 O9LM, WD G4 O9LM
 Beveled Dome Lensed			4101 ABZ 4" Decorative Beveled Dome Lens Trim - Classic Aged Bronze 4101 SC 4" Decorative Beveled Dome Lens Trim - Satin Chrome 4101 WH 4" Decorative Beveled Dome Lens Trim - White	IC1/ IC1 W/ IC1 S: 50W PAR20, 30W R20 IC1P /TC1/ TC1 S/ TC1R: 50W PAR20, 50W R20 TC1RC W : 50W PAR20, APT1: 50W PAR20, 50W R20 ICPL4: 26W, 18W PL4: 26W, 18W IC1LED: G4 O6LM, WD G4N O6LM/G4 O9LM, WD G4 O9LM IC1RLED: G4 O6LM, WD G4N O6LM/G4 O9LM, WD G4 O9LM
 Frosted Glass			4181 CLEAR 4" Decorative Frosted Glass Trim - Perimeter Frosted Clear Glass	IC1/ IC1 W/ IC1 S: 30W R20, 35W PAR20 IC1P /TC1/ TC1 S/ TC1R: 50W PAR20, 50W R20 APT1: 50W PAR20, 50W R20

Housing and trim can be ordered together or separate, but will always ship separately.