



THE PROFESSIONAL STANDARD

PRODUCT SELECTION GUIDE

Can't Decide? Check the Guide!



SMOKE ALARMS

Model	Smoke Sensor	Battery Type	Latching Alarm Indicator	End-of-Life Signal	Single Test/Silence Button	Limited Warranty
120V Hardwired (includes battery backup if listed under battery type)						
▶ 7020BSLA (1036168)	Photo/Strobe	10-Year Sealed Lithium	✓	✓	✓	10 Years
▶ 9120BA	Ion	9V Carbon Zinc	✓		✓	10 Years
9120LBLA	Ion	10-Year Lithium	✓	✓	✓	10 Years
7010BA	Photo	9V Carbon Zinc	✓		✓	10 Years
3120BA (1044566)	Ion/Photo	Two AA Alkaline	✓		✓	10 Years
7016BTCA	Photo	9V Carbon Zinc	✓		✓	10 Years
Battery Operated						
FG250BA/FG250CNA (1039880)	Ion	9V Carbon Zinc			✓	10 Years
SA303CNA (1039802)	Ion	9V Alkaline			✓	10 Years
SA304CNA (1039801) (Escape Light Unit)	Ion	9V Alkaline			✓	10 Years
SA3210A (1039840)	Photo/Ion	10-Year Sealed Lithium	✓	✓	✓	10 Years
PR700A-6 (1039769)	Photo	9V Carbon Zinc			✓	10 Years
PR710A-6 (1039848)	Photo	10-Year Sealed Lithium		✓	✓	10 Years
Wireless Interconnect						
SA520CNA-3ST (1039832) (Hardwired)	Photo	Two AA Alkaline Backup	✓		✓	10 Years
SA500CNA-3ST (1039831) (Battery Operated)	Photo	Two AA Alkaline	✓		✓	10 Years

FEATURED PRODUCTS



▶ 7020BSLA (1036168)

- Hardwired 2-in-1 Smoke & LED Strobe Alarm with 10-Year Sealed Lithium Battery Backup**
- Photoelectric Smoke Sensing Technology
 - 10-Year Sealed Lithium Battery Backup
 - Smart LED Strobe – Separate Flash Patterns for Smoke and Carbon Monoxide
 - 10-Year Limited Warranty



▶ 9120BA

- Hardwired Smoke Alarm with Battery Backup**
- Ionization Smoke Sensing Technology
 - 9V Battery Backup
 - Two Locking Features – Pins Are Provided to Lock Battery Drawer and/or Alarm to Base
 - Latching Alarm Indicator – Remembers Which Unit Initiated an Alarm
 - 10-Year Limited Warranty

Model	Smoke Sensor	Battery Type	Electrochemical CO Sensor	Voice Location	Latching Alarm Indicator	End-of-Life Signal	Single Test/Silence Button	Limited Warranty
120V Hardwired (Includes Battery Backup If Listed Under Battery Type)								
► 7030BSLA (1038871)	Photo/Strobe/CO	10-Year Sealed Lithium	✓		✓	✓	✓	10 Years
► SC9120BA	Ion	9V Alkaline	✓		✓	✓	✓	10 Years
SC9120LBLA	Ion	10-Year Lithium	✓		✓	✓	✓	10 Years
SC9126BTCA	Ion	9V Alkaline	✓		✓	✓	✓	10 Years
SC7010BA	Photo	Two AA Alkaline	✓		✓	✓	✓	7 Years
SC7016BTCA	Photo	Two AA Alkaline	✓		✓	✓	✓	7 Years
SC7010BVA	Photo	Two AA Alkaline	✓	✓	✓	✓	✓	10 Years
Battery Operated								
PRC700A-6 (1039778)	Photo	Two AA Alkaline	✓			✓	✓	7 Years
PRC700VA-6 (1039781)	Photo	Two AA Alkaline	✓	✓		✓	✓	7 Years
PRC710A-6 (1039860)	Photo	10-Year Sealed Lithium	✓			✓	✓	10 Years
PRC710VA-6 (1039862)	Photo	10-Year Sealed Lithium	✓	✓		✓	✓	10 Years
Wireless Interconnect								
SC0500NVA (1039823) (Battery Operated)	Photo	Two AA Alkaline	✓		✓	✓	✓	7 Years
Connected Safety								
1042253 (Battery Operated)	Photo	First Alert 3 Cell Lithium	✓	✓		✓	✓	5 Years

COMBINATION ALARMS

FEATURED PRODUCTS



► 7030BSLA (1038871)

Hardwired 3-in-1 Smoke, Carbon Monoxide & LED Strobe Alarm with 10-Year Sealed Lithium Battery Backup

- Photoelectric Smoke Sensing Technology
- Electrochemical Carbon Monoxide Sensor
- 10-Year Sealed Lithium Battery Backup
- Smart LED Strobe - Separate Flash Patterns for Smoke and Carbon Monoxide
- 10-Year Limited Warranty



► SC9120BA

Hardwired Ion Smoke & Carbon Monoxide Combination Alarm with Battery Backup

- Ionization Smoke Sensing Technology
- Electrochemical Carbon Monoxide Sensor
- Two Latching Features - Alarm Latch: Remembers and Identifies Initiating Alarms; Low Battery: Identifies Affected Unit
- Perfect Mount - Allows for Easy Alignment of Alarm
- 10-Year Limited Warranty

CARBON MONOXIDE ALARMS	Model	Battery Type	Electrochemical CO Sensor	Digital Display	Latching Alarm Indicator	End-of-Life Signal	Single Test/Silence Button	Limited Warranty	
	120V Hardwired (Includes Battery Backup If Listed Under Battery Type)								
	► C05120BNA	9V Alkaline	✓		✓	✓	✓	7 Years	
	Battery Operated								
	► C0400A (1039934)	Two AA Alkaline	✓			✓	✓	7 Years	
	C04106A (1039724)	Two AA Alkaline	✓	✓		✓	✓	7 Years	
	C0710A (1039749)	10-Year Sealed Lithium	✓	✓		✓	✓	10 Years	
	Plug-in (Includes Battery Backup If Listed Under Battery Type)								
	C0600A (1039196)	Plug-in ONLY	✓			✓	✓	7 Years	
	C0605A (1039731)	Two AA Alkaline	✓			✓	✓	7 Years	
C0615A (1039742)	Two AA Alkaline	✓	✓		✓	✓	7 Years		
GC016CNA (1039758) (Explosive Gas/CO Combo Alarm)	9V Alkaline	✓	✓		✓	✓	5 Years		

LED STROBES	Model	Smoke Sensor	Battery Type	Electrochemical CO Sensor	Latching Alarm Indicator	End-of-Life Signal	Single Test/Silence Button	Limited Warranty	
	120V Hardwired (Includes Battery Backup If Listed Under Battery Type)								
	7020BSLA (1036168)	Photo/Strobe	10-Year Sealed Lithium		✓	✓	✓	10 Years	
	7030BSLA (1038871)	Photo/Strobe/CO	10-Year Sealed Lithium	✓	✓	✓	✓	10 Years	
	Strobe Only								
	SLED177A (1038604)	Strobe ONLY	Hardwired ONLY					10 Years	

FEATURED PRODUCTS



- **C05120BNA**
Hardwired Carbon Monoxide Alarm with Battery Backup
- Electrochemical Carbon Monoxide Sensor
 - 9V Alkaline Battery Backup
 - Two Latching Features – Alarm Latch: Remembers and Identifies Initiating Alarms; Low Battery: Identifies Affected Unit
 - End-of-Life Signal
 - 7-Year Limited Warranty



- **C0400A (1039934)**
Battery Operated Carbon Monoxide Alarm
- Electrochemical Carbon Monoxide Sensor
 - Two AA Batteries
 - Two Silence Features – Silences Low Battery Chirps for Up to Eight Hours or Temporarily Silences Nuisance Alarms
 - End-of-Life-Signal
 - 7-Year Limited Warranty