

ATTACHED RING CRIMP CONNECTORS

FOR SERIES 59 CABLE : SERIES 6 CABLE : SERIES 11 CABLE



SERIES 59 CABLE

MODEL #	DESCRIPTION	PLATING	CRIMP TOOL HEX SIZE
F59-290G	F Male / Brass	Gold Iridite	.324
F59-290D	F Male / Zinc Nut	Nickel	.324
F59-290CC	F Male / Brass / Conical Crimp	Tin	Uses RTC-360 or Similar
RCA59-290	RCA Male / Fixed Pin / 1 Piece	Nickel	.324
RCA59-290G	RCA Male / Fixed Pin / 1 Piece	Gold	.324
BNC-C290	BNC Male / Fixed Pin / 1 Piece	Nickel	.324
F59-UNIV	F Male / Brass / Universal	Gold Iridite	.360



SERIES 6 CABLE

MODEL #	DESCRIPTION	PLATING	CRIMP TOOL HEX SIZE
F56-324G	F Male / Brass	Gold Iridite	.324
F56-324T	F Male / Brass	Tin	.324
F56-324D	F Male / Zinc Nut	Nickel	.324
F56-324	F Male / Zinc Nut	Gold Iridite	.324
F6-324	F Male / Economy	Nickel	.324
F56-324CC	F Male / Brass / Conical Crimp	Tin	Uses RTC-360 or Similar
F56-324CCWP	F Male / Brass / Conical Crimp with O-Ring	Tin	Uses RTC-360 or Similar
F56-324K	F Male / Brass / Knurled Nut	Tin	.324
F56-342G	F Male / Brass / Tri Shield	Gold Iridite	.324
F56-342T	F Male / Brass / Tri Shield	Tin	.324
F56-357G	F Male / Brass / Quad Shield	Gold Iridite	.360
F56-357T	F Male / Brass / Quad Shield	Tin	.360
F56-UNIV	F Male / Brass / Universal	Gold Iridite	.360
F-5681G	F Female / 1 Piece / High Return Loss	Gold Iridite	.324
BNC-C324	BNC Male / Fixed Pin / 1 Piece	Nickel	.324

ATTACHED RING CRIMP CONNECTORS



SERIES 11 CABLE

MODEL #	DESCRIPTION	PLATING	CRIMP TOOL HEX SIZE
F11-460	F Male / Fixed Pin	Tin	.472
F11-480	F Male / Fixed Pin / Quad Shield	Tin	.472
F11-460WOL	F Male / Fixed Pin with O-Ring and Gel	Tin	.472



SERIES 59 & 6 MOISTURE RESISTANT

MODEL #	DESCRIPTION	PLATING	CRIMP TOOL HEX SIZE
F59-290WOL	F Male / Brass / O-Ring and Gel	Gold Iridite	.324
F6-324WL	F Male / Economy / Large Nut / O-Ring and Gel	Gold Iridite	.324
F56-324W	F Male / Brass / Zinc Nut / O-Ring and Gel	Gold Iridite	.324
F56-324WOL	F Male / Brass / 4 Turn Nut / O-Ring and Gel	Gold Iridite	.324
F56-324WL	F Male / Brass / Large Nut / O-Ring and Gel	Gold Iridite	.324
F56-324GWP	F Male / Brass / 4 Turn Nut / O-Ring	Gold Iridite	.324
F56-UNIV-WL	F Male / Brass / Universal / Large Nut O-Ring and Gel	Gold Iridite	.360

MCV CONNECTORS

The Holland connector line offers customers the flexibility to use one connector to fit a variety of different sizes of cable. Our **MCV Series** (Multiple Cable Version) compression connectors are available in the configurations shown below.

