



Core & Coil (71A) HPS ~LT~ 200W

CORE & COIL HID HPS BAL 150W S55 120V KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information	
ANSI Code	S55
Lamp Type	150W HPS
Number of Lamps	1 piece/unit
Circuit Type	R-HPF
Ballast Type	Magnetic HID
Base Model	71A8107B
Core Size	2 5/8 x 2 3/16
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	INTEGRAL
Ignitor Temperature Rating	125°C
Capacitor Value	55 MFD
Capacitor Catalog Number	7C550P12RA
Capacitor Requirements	120V
Capacitor Temperature Rating	105°C
Capacitor Diameter/Oval Dimensions	1.75 in
Capacitor Height	3.75 in
Automatic Restart	No
Operating and Electrical	
Input Voltage	120 V

Input Frequency	60 Hz			
Input Current (Open Circuit)	2.35 A			
Input Current (Starting)	2.25 A			
Input Current (Short Circuit)	1.65-2.75 A			
Secondary Short Circuit Current	3.65-5.55 A			
Constant Wattage Deviation	Within Trapezoid			
Ballast Factor (Nom)	1			
Power Factor (Nom)	0.90			
Open Circuit Voltage	120 V			
Input Current (Nom)	1.5 A A			
Input Power (Nom)	170 W			
Rated Lamp Power	150 W			
Wiring				
Wire Striplength	0.5 mm			
Wire Length by Color	12"			
Wire Type	Stranded			
Remote Wiring Configuration Allowed	Yes			
Max Ballast-Lamp Distance Remote Wiring 2'				
Recommended Fuse Value	15 A			

Core & Coil (71A) HPS ~LT~ 200W

Approval and Application	
Open Circuit Voltage Test (Volts)	114-126 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	A
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029A
Product Data	


KIT

CORE & COIL HID HPS BAL 150W S55 120V

EAN/UPC - Product	781087026311
Order code	913700500911
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913700500911
Net Weight (Piece)	1.847 kg

Order product name

Dimensional drawing



HPS BAL 150W S55 120V KIT

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID HPS BAL 150W S55 120V	3.6 in	2 in	2.6 in	2.2 in	2.2 in	1.8 in
КІТ						



 \odot 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com 2019, March 22 - data subject to change