

Distribution circuit-breakers

SACE XT4V (150kA) TMF/TMA Front terminals (F)



XT4 - circuit-breaker

Size	lu	Trip units	In	Type	3 poles	4 poles
					Code	Code
XT4	250	TMF	25	XT4V 250 TMF 25-400	1SDA075291R1	1SDA075308R1
			30	XT4V 250 TMF 30-400	1SDA075292R1	1SDA075309R1
			35	XT4V 250 TMF 35-400	1SDA075293R1	1SDA075310R1
			40	XT4V 250 TMF 40-400	1SDA075294R1	1SDA075311R1
			50	XT4V 250 TMF 50-500	1SDA075295R1	1SDA075312R1
			60	XT4V 250 TMF 60-600	1SDA075296R1	1SDA075313R1
			70	XT4V 250 TMF 70-700	1SDA075297R1	1SDA075314R1
			80	XT4V 250 TMF 80-800	1SDA080160R1	
			90	XT4V 250 TMF 90-900	1SDA080161R1	
			100	XT4V 250 TMF 100-1000	1SDA080152R1	
			110	XT4V 250 TMF 110-1100	1SDA080153R1	
			125	XT4V 250 TMF 125-1250	1SDA080154R1	
			150	XT4V 250 TMF 150-1500	1SDA080155R1	
			175	XT4V 250 TMF 175-1750	1SDA080156R1	
			200	XT4V 250 TMF 200-2000	1SDA080157R1	
			225	XT4V 250 TMF 225-2250	1SDA080158R1	
			250	XT4V 250 TMF 250-2500	1SDA080159R1	
XT4	250	TMA	80	XT4V 250 TMA 80-800	1SDA075298R1	1SDA075315R1
			90	XT4V 250 TMA 90-900	1SDA075299R1	1SDA075316R1
			100	XT4V 250 TMA 100-1000	1SDA075300R1	1SDA075317R1
			110	XT4V 250 TMA 110-1100	1SDA075301R1	1SDA075318R1
			125	XT4V 250 TMA 125-1250	1SDA075302R1	1SDA075319R1
			150	XT4V 250 TMA 150-1500	1SDA075303R1	1SDA075320R1
			175	XT4V 250 TMA 175-1750	1SDA075304R1	1SDA075321R1
			200	XT4V 250 TMA 200-2000	1SDA075305R1	1SDA075322R1
			225	XT4V 250 TMA 225-2250	1SDA075306R1	1SDA075323R1
			250	XT4V 250 TMA 250-2500	1SDA075307R1	1SDA075324R1

SACE XT4V (150kA) Ekip LS/I Front terminals (F)

Size	lu	Trip units	In	Type	3 poles	4 poles
					Code	Code
XT4	250	Ekip LS/I	40	XT4V 250 Ekip LS/I In=40A	1SDA075406R1	1SDA075412R1
			60	XT4V 250 Ekip LS/I In=60A	1SDA075407R1	1SDA075413R1
			100	XT4V 250 Ekip LS/I In=100A	1SDA075408R1	1SDA075414R1
			150	XT4V 250 Ekip LS/I In=150A	1SDA075409R1	1SDA075415R1
			225	XT4V 250 Ekip LS/I In=225A	1SDA075410R1	1SDA075416R1
			250	XT4V 250 Ekip LS/I In=250A	1SDA075411R1	1SDA075417R1