

Wire connector TC1.1 14 AWG...2/0 Cu with control wire voltage tap-off 3 units accessories for: 3VA4/5 125



Model	
product brand name	SETRON
product designation	accessories
design of the product	circular conductor terminal
accessories	Wire connector
General technical data	
designation / of the terminal	TC1.1
type of electrical connection / with control wire tap	Yes
Connections according IEC	
stripped length	12,2 mm
Connections according UL	
permissible temperature / of connectable conductor / according to UL 486A-486B	90 °C
stripped length	0.48 in
connectable conductor cross-section	
<ul style="list-style-type: none"> <li>for copper cable / solid / minimum</li> <li>for copper cable / solid / maximum</li> <li>for copper cable / stranded / minimum</li> <li>for copper cable / stranded / maximum</li> </ul>	14 AWG 10 AWG 14 AWG 2/0 AWG
tightening torque / when using copper cables	
<ul style="list-style-type: none"> <li>solid</li> <li>stranded</li> </ul>	14 AWG: 25 lb-in 12 AWG: 35 lb-in 10 AWG: 55 lb-in 14 AWG: 25 lb-in 12 AWG: 35 lb-in 10 AWG - 2/0: 55 lb-in

Certificates		
General Product Approval	EMC	Declaration of Conformity



[Miscellaneous](#)



Marine / Shipping	other	Environment		
-------------------	-------	-------------	--	--



LRS

[Miscellaneous](#)

[Confirmation](#)

[Miscellaneous](#)

[Environmental Confirmations](#)

### Further information

Siemens has decided to exit the Russian market (see here).  
<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

**Siemens is working on the renewal of the current EAC certificates.**

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

**Information on the packaging**

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9133-0JK11>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9133-0JK11>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3VA9133-0JK11](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9133-0JK11)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



---

last modified:

10/25/2023 

