



2488SW8804



541901



2577SW000H



2577SW000X



547703

EXTENSION CORDS W/ POWER LIGHT INDICATOR

| Stock # | Gauge/Conductors | Wire Type | Length (ft) | Length (m) | Cord Color | Amps | Case Pack Quantity |
|------------|------------------|-----------|-------------|------------|-----------------------|------|--------------------|
| 540836** | 14/3 | STW | 3' | 0.9 m | Red/Black | 15 | 12 |
| 541901** | 14/3 | SJTW | 22' | 7 m | Red/Black | 15 | 6 |
| 2487SW8804 | 14/3 | SJTW | 25' | 7.6 m | Red | 15 | 12 |
| 2488SW8804 | 14/3 | SJTW | 50' | 15.2 m | Red | 15 | 6 |
| 541902** | 14/3 | SJTW | 50' | 15.2 m | Red/Black | 15 | 5 |
| 54800401** | 14/3 | SJTW | 50' | 15.2 m | Neon Pink | 13 | 13 |
| 521* | 14/3 | SJTW | 50' | 15.2 m | Yellow/Black | 15 | 13 |
| 2489SW8804 | 14/3 | SJTW | 100' | 30.5 m | Red | 13 | 6 |
| 541909** | 14/3 | SJTW | 100' | 30.5 m | Red/Black | 15 | 3 |
| | | | | | | | |
| 2577SW000H | 12/3 | SJTW | 25' | 7.6 m | Cool Blue | 15 | 12 |
| 2577SW000X | 12/3 | SJTW | 25' | 7.6 m | Cool Green | 15 | 12 |
| 547703** | 12/3 | SJTW | 25' | 7.6 m | Dark Green/Yellow | 15 | 12 |
| 2577SW000A | 12/3 | SJTW | 25' | 7.6 m | Cool Pink | 15 | 12 |
| 2587SW8802 | 12/3 | SJTW | 25' | 7.6 m | Yellow | 15 | 12 |
| | | | | | | | |
| 2578SW000H | 12/3 | SJTW | 50' | 15.2 m | Cool Blue | 15 | 8 |
| 2548SW0064 | 12/3 | SJTW | 50' | 15.2 m | Cool Blue/Red | 15 | 8 |
| 2548SW00HX | 12/3 | SJTW | 50' | 15.2 m | Cool Blue/Cool Green | 15 | 8 |
| 2548SW0052 | 12/3 | SJTW | 50' | 15.2 m | Dark Green/Yellow | 15 | 8 |
| 2548SW0054 | 12/3 | SJTW | 50' | 15.2 m | Lime Green/Red | 15 | 8 |
| 2578SW000X | 12/3 | SJTW | 50' | 15.2 m | Cool Green | 15 | 8 |
| 2548SW003V | 12/3 | SJTW | 50' | 15.2 m | Cool Orange/Cool Blue | 15 | 8 |
| 2578SW000A | 12/3 | SJTW | 50' | 15.2 m | Cool Pink | 15 | 8 |
| 2548SW0077 | 12/3 | SJTW | 50' | 15.2 m | Cool Pink/Lime Green | 15 | 8 |
| 2548SW0041 | 12/3 | SJTW | 50' | 15.2 m | Red/White | 15 | 8 |
| 2588SW0002 | 12/3 | SJTW | 50' | 15.2 m | Yellow | 15 | 6 |
| 2548SW0022 | 12/3 | SJTW | 50' | 15.2 m | Yellow/Purple | 15 | 8 |
| 550523* ** | 12/3 | SJTW | 50' | 15.2 m | Yellow/Black | 15 | 6 |
| | | | | | | | |
| 25850002 | 12/3 | SJTW | 80' | 24.4 m | Yellow | 15 | 4 |
| | | | | | | | |
| 2549SW0064 | 12/3 | SJTW | 100' | 30.5 m | Cool Blue/Red | 15 | 4 |
| 2579SW000H | 12/3 | SJTW | 100' | 30.5 m | Cool Blue | 15 | 4 |
| 2549SW0054 | 12/3 | SJTW | 100' | 30.5 m | Lime Green/Red | 15 | 4 |
| 2579SW000X | 12/3 | SJTW | 100' | 30.5 m | Cool Green | 15 | 4 |
| 2549SW0052 | 12/3 | SJTW | 100' | 30.5 m | Dark Green/Yellow | 15 | 4 |
| 2549SW003V | 12/3 | SJTW | 100' | 30.5 m | Cool Orange/Cool Blue | 15 | 4 |
| 2549SW0077 | 12/3 | SJTW | 100' | 30.5 m | Cool Pink/Lime Green | 15 | 4 |
| 2579SW000A | 12/3 | SJTW | 100' | 30.5 m | Cool Pink | 15 | 4 |
| 2549SW0041 | 12/3 | SJTW | 100' | 30.5 m | Red/White | 15 | 4 |
| 2549SW0022 | 12/3 | SJTW | 100' | 30.5 m | Yellow/Purple | 15 | 4 |
| 2589SW0002 | 12/3 | SJTW | 100' | 30.5 m | Yellow | 15 | 4 |
| | | | | | | | |
| 2687SW0002 | 10/3 | SJTW | 25' | 7.6 m | Yellow | 15 | 6 |
| 26480064 | 10/3 | SJTW | 50' | 15.2 m | Cool Blue/Red | 15 | 4 |
| 26480054 | 10/3 | SJTW | 50' | 15.2 m | Lime Green/Red | 15 | 4 |
| 2688SW0002 | 10/3 | SJTW | 50' | 15.2 m | Yellow | 15 | 4 |
| 26490064 | 10/3 | SJTW | 100' | 30.5 m | Cool Blue/Red | 15 | 3 |
| 26490054 | 10/3 | SJTW | 100' | 30.5 m | Lime Green/Red | 15 | 3 |
| 2689SW0002 | 10/3 | SJTW | 100' | 30.5 m | Yellow | 15 | 3 |

*Black Plugs

**Product packaging is advertised in Meters