

# Special Purpose Products

**Plymouth**

## 20 PLYSIL® Silicone Rubber Tape

Cat.	Dimensions	Packaging	Weight
3455	1" x .020" x 30' 25mm x 0,51mm x 9m	50/case C	18 lbs 8 kg

## 53 PLYARC® Arc and Fireproofing Tape

Cat.	Color	Dimensions	Packaging	Weight
3817	Grey	1 1/2" x .030" x 20' 38mm x 0,76mm x 6m	20/case C	12 lbs 5 kg
3819	Grey	3" x .030" x 20' 76mm x 0,76mm x 6m	10/case C	12 lbs 5 kg

## 77 PLYGLAS® Pressure Sensitive Glass Cloth Tape

Cat.	Dimensions	Packaging	Weight
3451	1/2" x .007" x 66' 13mm x 0,18mm x 20m	50/case B	9 lbs 4 kg
3456	3/4" x .007" x 66' 19mm x 0,18mm x 20m	50/case B	12 lbs 5 kg
3459	1" x .007" x 108' 25mm x 0,18mm x 33m	20/case B	37 lbs 17 kg

## 61 and 61A Varnished Dacron Glass Tape

Cat.	Dimensions	Packaging	Weight
1101 (without adhesive)	3/4" x .007" x 60' 19mm x 0,18mm x 18m	40/case B	9 lbs 4 kg
1102 (without adhesive)	1" x .007" x 108' 25mm x 0,18mm x 33m	6/case	4 lbs 2 kg
1103 (without adhesive)	1 1/2" x .007" x 108' 38mm x 0,18mm x 33m	6/case B	16 lbs 7 kg
1121 (with adhesive)	3/4" x .008" x 60' 19mm x 0,20mm x 18,2m	40/case B	9 lbs 4 kg
1122 (with adhesive)	1" x .008" x 108' 25mm x 0,20mm x 33m	6/case	4 lbs 2 kg
1123 (with adhesive)	1 1/2" x .008" x 108' 38mm x 0,20mm x 33m	6/case B	16 lbs 7 kg

## 44 NEOPRENE Jacketing Tape

Cat.	Dimensions	Packaging	Weight
8261	3/4" x .030" x 30' 19mm x 0,76mm x 9m	100/case C	54 lbs 24 kg
8263	1 1/2" x .030" x 30' 38mm x 0,76mm x 9m	50/case C	55 lbs 25 kg
8264	2" x .030" x 30' 51mm x 0,76mm x 9m	40/case C	57 lbs 26 kg

## PLYPREP™ Cable Preparation Kit

Cat.	Contents	Packaging	Weight
2684	1 kit/bag	20/case	4 lbs 2 kg

## TERMINAL WRAP

Cat.	Range	Packaging	Weight
9012	2-25kV/.55"-.95" dia. 14,1-24,1mm dia.	20/case B	8 lbs 4 kg



**Need to Arc and Fireproof Cables?**

Plymouth Tape offers multiple solutions to arc and fireproofing, including 53 Plyarc® arc and fireproofing tape.