



PANDUIT<sup>®</sup>

building a smarter, unified business foundation

Connect. Manage. Automate.

## PANDUIT®

## NetKey® Cabling System

The NetKey® Copper and Fiber Cabling System provides a complete, standards compliant cabling infrastructure solution for voice, data and video applications. NetKey® Modules feature the universal "keystone" design and are compatible with a wide assortment of modular patch panels, faceplates and surface mount boxes. When teamed with complementary Panduit products, the NetKey® solutions cover all your needs from the telecommunication room to the work area with the proven innovation and quality you depend on from Panduit.



Panduit and General Cable™ offer a comprehensive line of contractor-grade connectivity and cabling solutions. This world-class partnership provides guaranteed network performance and system reliability for customer requirements.

For the complete cable offering, reference the NetGen® Structured Cabling Solutions Brochure, SA-NCCB16.

General Cable is a trademark of General Cable Technologies Corporation. NetGen is a registered trademark of General Cable Technologies Corporation and Panduit.

Panduit and NetKey are registered trademarks of Panduit Corp.







Off White

Off White

## NetKey® Category 6, 5e and 3 Jack Modules

- Meet all industry performance standards for Category 6, 5e and 3
- Punchdown jack modules are 100% performance tested and individually serialized for future traceability
- · Snap in and out of keystone openings for easy moves, adds and changes
- Universal label includes T568A and T568B wiring schemes



NK688MBL NKP5E88MBL



NK688MBL-Q NKP5E88MBL-Q



NK5E88MIWY



NK5E88MBU-Q



NK388MIWY



NK366UMIWY



NK366MIWY

Part Number	Description	Color
NetKey® Catego	ry 6 UTP Jack Modules*	
NK688MBL	Category 6, 8-position, 8-wire, keystone punchdown jack module.	Black
NK688MBL-Q	Convenience pack of 25, Category 6, 8-position, 8-wire, keystone punchdown jack modules.	Black
NetKey® Catego	ry 5e UTP Jack Modules*	
NKP5E88MBL	Category 5e, 8-position, 8-wire, keystone punchdown jack module.	Black
NKP5E88MBL-Q	Convenience pack of 25, Category 5e, 8-position, 8-wire, keystone punchdown jack modules.	Black
NK5E88MIWY	Category 5e, 8-position, 8-wire, keystone leadframe jack module.	Off White
NK5E88MBU-Q	Convenience pack of 25, Category 5e, 8-position, 8-wire, keystone leadframe jack modules.	Blue
NetKey® Catego	ry 3 UTP Jack Modules**	
NK388MIWY	Category 3, 8-position, 8-wire, keystone leadframe jack module.	Off White

Category 3, 6-position, 6-wire, keystone leadframe jack module. \*For standard colors replace color suffix with IW (Off White), EI (Electric Ivory), IG (International Gray), WH (White), BL (Black), BU (Blue), RD (Red), YL (Yellow), GR (Green), OR (Orange) or VL (Violet).

Category 3, 6-position, 6-wire, keystone leadframe jack module.

Termination cap color-coded to USOC wiring scheme.

NK366UMIWY

NK366MIWY

## NetKey® Copper UTP Patch Cords

- Meet all industry performance standards for Category 6 and 5e
- · Available in a variety of colors and lengths for design flexibility

• 100% performance tested



NK6PC^\*Y



NK5EPC^\*Y

Part Number	Description	
Category 6		
NK6PC^*Y	Category 6, UTP patch cord with modular plugs on each end.	
Category 5e		
NK5EPC^*Y	Category 5e, UTP patch cord with modular plugs on each end.	

<sup>^</sup>Available in 3, 5, 7, 10, 14 and 20 foot lengths.

To order convenience package of 25 jack modules, add –Q to end of part number. \*\* For standard colors replace color suffix with IW (Off White), EI (Electric Ivory), IG (International Gray), WH (White) or BL (Black).

Termination tools found on page 13.

<sup>\*</sup>For standard colors other than Off White, add suffix BU (Blue), RD (Red), YL (Yellow) or GR (Green) before Y in the part number. For example, the part number of a blue, Category 6, 5-foot patch cord is NK6PC5BUY.