



# Core & Coil (71A) HPS ~GT~ 400W

## CORE & COIL HID HPS BAL 1000W S52 120/277/347V KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

#### **Product data**

General Information	
	653
ANSI Code	S52
Lamp Type	1000W HPS
Number of Lamps	1 piece/unit
Circuit Type	CWA
Ballast Type	Magnetic HID
Base Model	71A87A3
Core Size	4 1/4 x 6
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	LI571-H5
Ignitor Temperature Rating	105°C
Capacitor Value	26 MFD
Capacitor Catalog Number	RW1626020
Capacitor Requirements	525V
Capacitor Temperature Rating	90℃
Capacitor Diameter/Oval Dimensions	1.75 in
Capacitor Height	4.25 in
Automatic Restart	No

Operating and Electrical					
Input Voltage	120/277/347 V				
Input Frequency	60 Hz				
Input Current (Open Circuit)	3.7/1.4/1.1 A				
Input Current (Starting)	6.4/2.8/2.2 A				
Input Current (Short Circuit)	6.9-10.4/3-4.6/2.5-3.7 A				
Secondary Short Circuit Current	6.4-7.8 A				
Constant Wattage Deviation	Within Trapezoid				
Ballast Factor (Nom)	1				
Power Factor (Nom)	0.90				
Open Circuit Voltage	435 V				
Input Current (Nom)	9.5/4.2/3.3 A A				
Input Power (Nom)	1100 W				
Rated Lamp Power	1000 W				
Wiring					
Wire Striplength	0.5 mm				
Wire Length by Color	12"				
Wire Type	Stranded				
Remote Wiring Configuration Allowed	Yes				


Datasheet, 2019, March 22 data subject to change

### Core & Coil (71A) HPS ~GT~ 400W

Max Ballast-Lamp Distance Remote Wiring 15'					
Recommended Fuse Value	25/15/10 A				
Approval and Application					
Open Circuit Voltage Test (Volts)	395-485 V				
Approval Marks	ULR CSA certificate RoHS Compliant				
Temperature Marking	C/C/C				
UL Recognized	Yes				
Hipot Test (1 Minute)	2000 V				
Hipot Test (2 Seconds)	2500 V				
UL Insulation Class	H(180°C)				
UL Temperature Code	1029C				

Product Data					
Order product name	CORE & COIL HID HPS BAL 1000W S52				
	120/277/347V KIT				
EAN/UPC - Product	781087037485				
Order code	913700526909				
Numerator - Quantity Per Pack	1				
Numerator - Packs per outer box	1				
Material Nr. (12NC)	913700526909				
Net Weight (Piece)	13.731 kg				

#### Dimensional drawing



HPS BAL 1000W S52 120/277/347V KIT

Product	<b>C</b> 1	C2	A1	A2	А3	B1	B2
CORE & COIL HID HPS BAL 1000W	5.9 in	3.90 in	6 in	5.4 in	4.4 in	4.3 in	3.9 in
S52 120/277/347V KIT							

