



Core & Coil (71A) HPS ~LT~ 200W

CORE & COIL HID HPS BAL 70W S62 QUAD C&C

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information				
ANSI Code	S62			
Lamp Type	70W HPS			
Number of Lamps	1 piece/unit			
Circuit Type	HX-HPF			
Ballast Type	Magnetic HID			
Base Model	71A7991			
Core Size	3 X 4 (2 LW)			
Suitable For Outdoor Use	Yes			
Ignitor Catalog Number	LI551-H4			
Ignitor Temperature Rating	105°C			
Capacitor Value	7 MFD			
Capacitor Catalog Number	7C070L30RA			
Capacitor Requirements	280V			
Capacitor Temperature Rating	105°C			
Capacitor Diameter/Oval Dimensions	1.25 in			
Capacitor Height	2.75 in			
Automatic Restart	No			
Operating and Electrical				
Input Voltage	120/208/240/277 V			

Input Frequency	60 Hz
Input Current (Open Circuit)	1.46/0.86/0.73/0.64 A
Input Current (Starting)	0.85/0.51/0.43/0.39 A
Input Current (Short Circuit)	0.6-0.95/0.35-0.6/0.3-0.5/0.25-0.4 A
Secondary Short Circuit Current	2.1-2.45 A
Constant Wattage Deviation	Within Trapezoid
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Open Circuit Voltage	120 V
Input Current (Nom)	0.81/0.47/0.4/0.35 A A
Input Power (Nom)	96 W
Rated Lamp Power	70 W
Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes
Max Ballast-Lamp Distance Remote	2'
Wiring	


Datasheet, 2019, March 22 data subject to change

Core & Coil (71A) HPS ~LT~ 200W

Recommended Fuse Value	5/3/2/2 A
Approval and Application	
Open Circuit Voltage Test (Volts)	110-130 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	B/C/B/C
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029C

Product Data	
Order product name	CORE & COIL HID HPS BAL 70W S62 QUAD C&C
EAN/UPC - Product	781087799154
Order code	913700576009
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	913700576009
Net Weight (Piece)	2.037 kg

Dimensional drawing



HPS BAL 70W S62 QUAD C&C

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID HPS BAL 70W S62	2.9 in	1.52 in	3.9 in	3.5 in	2.8 in	2.4 in
QUAD C&C						

