














Flush Mount

















Our decorative LED flush mount collection includes round and square trim styles that mount easily and seamlessly to the ceiling. They are ideal for use in residential single family & multi-family along with light commercial spaces. Perfect for foyers, hallways, bedrooms, offices, stairways and more.



	Application	Size	Description	Lumens (up to)	CCT	Mounting Options	CRI	Dimming	Finishes	Special Applications
Round										
	Indoor Single-Family Multi-Family Light Commercial	11"	Switchable, Round Decorative Flush Mount	1326	Switchable White 2700K 3000K 3500K 4000K 5000K	Ceiling	90	Phase Dimming down to 10%	Matte White Ships with extra Black Trim Ring	
	Indoor Single-Family Multi-Family Light Commercial	15"	Switchable, Square Decorative Flush Mount with Night- light	1840	Switchable White 2700K 3000K 3500K 4000K 5000K	Ceiling	90	Phase Dimming down to 10%	Matte White Ships with extra Black Trim Ring	
	Indoor Single-Family Multi-Family Light Commercial	13"	Static, Round Decorative Flush Mount	950	3000K 4000K	Ceiling	80	Works with most standard in- candescent dimmers	Brushed Nickel Antique Bronze	
		16"		1680						
	Indoor Single-Family Multi-Family Light Commercial	13"	Static, Square Decorative Flush Mount	1682	3000K 4000K	Ceiling	80	Works with most standard in- candescent dimmers	Brushed Nickel Antique Bronze	
	Indoor Single-Family Multi-Family Light Commercial	7"	Static, Round Decorative Flush Mount	612	2700K 3000K 3500K 4000K	Ceiling	80	Works with most standard in- candescent dimmers	Textured White Textured Bronze Natural Aluminum	
		13"		1900						
	Indoor Single-Family Multi-Family Light Commercial	7"	Switchable, Round Decorative Flush Mount	695	Switchable White 3000K 4000K 5000K	Ceiling	90	Works with most stan- dard incandescent dimmers	Textured White Natural Aluminum Dark Bronze	
	Indoor Single-Family Multi-Family Light Commercial	13"	Static, Square Decorative Flush Mount	1730	4000K	Ceiling	80	Works with most standard in- candescent dimmers	Textured White	



Flush Mount

	Application	Size	Description	Lumens (up to)	CCT	Mounting Options	CRI	Dimming	Finishes	Special Applications
Round										
 Lacuna (FMLACL)	Indoor Single-Family Multi-Family Light Commercial	14"	Static, Round Decorative Flush Mount	1400	3000K 4000K	Ceiling	80	Works with most standard in- candescent dimmers	Brushed Aluminum	
 Hildon (FMHLDL)	Indoor Single-Family Multi-Family Light Commercial	14"	Static, Round Decorative Flush Mount	2040	3000K 4000K	Ceiling	80	Works with most standard in- candescent dimmers	White	
 Bandon (FMBANL)	Indoor Single-Family Multi-Family Light Commercial	11"	Static, Round Decorative Flush Mount	1100	3000K 4000K	Ceiling	80	Works with most standard in- candescent dimmers	Chrome	
		14"		1600						
 Crenelle Round (FMCRNL)	Indoor Single-Family Multi-Family Light Commercial	14"	Static, Round Decorative Flush Mount	1535	3000K 4000K	Ceiling	80	Works with most standard in- candescent dimmers	Matte White	
 Crenelle Square (FMSCNL)	Indoor Single-Family Multi-Family Light Commercial	14"	Static, Square Deco- rative Flush Mount	1650	3000K 4000K	Ceiling	80	Works with most standard in- candescent dimmers	Matte White	
 LED Mushroom (FMMUSL)	Indoor Single-Family Multi-Family Light Commercial	9"	Static, Round Decorative Flush Mount	1400	3000K 4000K	Ceiling	80	Works with most standard in- candescent dimmers	White Polished Brushed Nickel Bronze	
 LED Globe (FMGLOL)	Indoor Single-Family Multi-Family Light Commercial	6"	Static, Round Decorative Flush Mount	526	3000K 4000K	Ceiling	80	Works with most standard in- candescent dimmers	Bronze	
 FMLRDL RD	Indoor Single-Family Multi-Family Light Commercial	11"	Static, Round Decorative Flush Mount	1400	3000K 4000K	Ceiling	80	Works with most standard in- candescent dimmers	White	
		20"		4000						



Linear

Our linear collection delivers a variety of styles and finishes to match any residential or light commercial aesthetic. They provide general illumination and are ideal for use in kitchens, offices, utility work areas, stairways and many others.



	Application	Size	Description	Lumens (up to)	CCT	CRI	Dimming	Mounting Options	Finishes	Special Applications
Linear										
 Lite Puff (FMLL)	Indoor Single-Family Multi-Family Light Commercial	9"	Linear Low Profile Flush Mount	4100	3000K 4000K	80	Dimmable 120V Triac Dim	Ceiling	Matte White	
		14"		4800						
 Cambridge (FMFL)	Indoor Single-Family Multi-Family Light Commercial	48"	Linear Deco-rative Flush Mount	3200	4000K	80	Use with non-dimmable switches only.	Ceiling	White Oak	
 Futra (FMLFUTL)	Indoor Single-Family Multi-Family Light Commercial	24"	Linear Deco-rative Flush Mount	2200	4000K	80	Works with most standard incandescent dimmers	Ceiling	Brushed Nickel	
		48"		3400						
 Saturn (FMFL)	Indoor Single-Family Multi-Family Light Commercial	48"	Linear Deco-rative Flush Mount	3200	4000K	80	Use with non-dimmable switches only.	Ceiling	Brushed Nickel Bronze	
 Vanderlyn (FMFL)	Indoor Single-Family Multi-Family Light Commercial	48"	Linear Deco-rative Flush Mount	3200	4000K	80	Use with non-dimmable switches only.	Ceiling	Bronze	



Linear

	Application	Size	Description	Lumens (up to)	CCT	CRI	Dimming	Mounting Options	Finishes	Special Applications
Linear										
 <p>Crest (FMLCRSL)</p>	Indoor Single-Family Multi-Family Light Commercial	48"	Switchable Linear Deco- rative Flush Mount	3900	Switchable White 3000K 4000K 5000K	90	Works with most standard incandescent dimmers	Ceiling	Brushed Nickel	
 <p>Catenary (FMLCCL)</p>	Indoor Single-Family Multi-Family Light Commercial	48"	Static Linear Decorative Flush Mount	3460	4000K	80	Works with most standard incandescent dimmers	Ceiling	Brushed Nickel	
 <p>Catenary SWW (FMLCCL)</p>	Indoor Single-Family Multi-Family Light Commercial	48"	Switchable Linear Deco- rative Flush Mount	3900	Switchable White 3000K 4000K 5000K	90	Works with most standard incandescent dim- mers	Ceiling	Brushed Nickel	



Vanity

Our decorative LED vanity collection delivers elegant and contemporary lighting designs. Luminaires are available in 1', 2', 3' and 4' nominal lengths. Vanity LED luminaires provide style, reliability, and the quality illumination needed in vanity applications. They are ideal for use in residential, commercial, hospitality, university, and multi-family settings.



	Application	Size	Description	Lumens (up to)	CCT	CRI	Dimming	Mounting Options	Finishes	Special Applications
Vanity										
 <p>Contemporary Square (FMVCSL)</p>	Indoor Single-Family Multi-Family Light Commercial	24"	Static, Square Decorative Vanity	1300	3000K	90	Use with non-dimmable switches only.	Wall Mount Vertically or Horizontally Backplate can be removed for a more low-profile design	Brushed Nickel	
		36"		3570						
 <p>Contemporary Square SWW (FMVCSLS)</p>	Indoor Single-Family Multi-Family Light Commercial	12"	Switchable, Square, Decorative Vanity	830	Switchable White 3000K 4000K 5000K	90	Dimmable by either triac or 0-10V dimming.	Wall Mount Vertically or Horizontally Backplate can be removed for a more low-profile design, see spec sheet	Brushed Nickel Chrome Bronze	
		24"		1740						
		36"		2560						
		48"		3200						
 <p>Contemporary Cylinder (FMVCL)</p>	Indoor Single-Family Multi-Family Light Commercial	24"	Static, Round Decorative Vanity	1400	3000K	90	Use with non-dimmable switches only.	Wall Mount Vertically or Horizontally Backplate can be removed for a more low-profile design	Brushed Nickel	
 <p>Contemporary Cylinder SWW (FMVCLS)</p>	Indoor Single-Family Multi-Family Light Commercial	12"	Switchable, Round Decorative Vanity	880	Switchable White 3000K 4000K 5000K	90	Dimmable by either triac or 0-10V dimming.	Wall Mount Vertically or Horizontally Backplate can be removed for a more low-profile design, see spec sheet	Brushed Nickel Chrome Matte Black	
		24"		1850						
		36"		2700						
		48"		3550						
 <p>Contemporary Arrow SWW (FMVCLS)</p>	Indoor Single-Family Multi-Family Light Commercial	24"	Switchable, Arrow Decorative Vanity	1700	Switchable White 3000K 4000K 5000K	90	Dimmable by either triac or 0-10V dimming.	Wall Mount Vertically or Horizontally Backplate can be removed for a more low-profile design	Brushed Nickel	