



# SLIMLED<sup>TM</sup>MULTI

**MULTI-APPLICATIONS, MULTI-COLORS, NOT SOLD SEPARATELY.**

Easily convert a standard octagon box or retrofit a traditional 4" or 6" downlight to an LED fixture. On-face magnets allows for securely attaching one of three included dead front magnetic faceplates (for 4" only). Perfect for multi-unit residential, the SLIMLED MULTI is also fire rated when installed into a fire rated octagon box.



## SQUARE TRIMS SOLD SEPERATELY

For 4" only.




\*Not available on high output option.



Models Shown: SLMT6-13W

## SlimLED MULTI 4"



### EVERYTHING IN 1 BOX




### DELIVERED

Up to 540 lm

### RATINGS



### TRIM COLORS



### SIZE



### TRIM



### CCT



### CRI

90

27, 30, 35, 40, 50 K

### COMPATIBLE HOUSING

- RF401 series
  - RF402 series
  - RF405 series
- OR
- Standard octagon box

### Ordering Guide

#### Selectable Output

**SLMT4-8W**




Highlighted option denotes QuickShip.

#### Square Trim


**SLMT4-ST\***

#### Finish




\*Square trim only, fixture sold separately

## SlimLED MULTI High Output



### EVERYTHING IN 1 BOX




### DELIVERED

Up to 750 lm

### RATINGS



### TRIM COLORS



### SIZE



### TRIM



### CCT



### CRI

80

### COMPATIBLE HOUSING

- Standard octagon box

### Ordering Guide

#### High Output

**SLMT4-8W**



Highlighted option denotes QuickShip.

#### Color Temperature

30K : 3000 K  
40K : 4000 K  
27K : 2700 K  
35K : 3500 K

**-HO**


#### Square Trim

**SLMT4-ST\***

BK : Black  
SL : Silver  
WH : White

\*Square trim only, fixture sold separately

## SlimLED MULTI 6"



6" CAN\*




J-BOX

\* Retrofit Kit sold separately for 13W version only (P-SLMT6-6CAN)

CCT switch accessible below the ceiling



### EVERYTHING IN 1 BOX



### DELIVERED


13W up to 1070lm

15W up to 1170lm

### RATINGS



### TRIM COLORS



### SIZE



### TRIM



### COLOR TEMPERATURE



### CRI

90

27, 30, 35, 40, 50 K

### COMPATIBLE HOUSING

- RF601ICAT series
  - RF602ICAT series
- OR
- Standard octagon box

### ACCESSORIES



#### P-SLMT6-6CAN

6" Housing accessories (Retrofit kit)  
E26 lampholder + wire + connectors + spring clips for 13W version only



#### SLMT6-RT-BK

Optional trim for 6" SlimLED Multi, Black.



#### SLMT6-RT-BN

Optional trim for 6" SlimLED Multi, Brushed Nickel.

### Ordering Guide

#### Standard



Highlighted option denotes QuickShip.

**SLMT6-13W**

#### Commercial



Highlighted option denotes QuickShip.

**SLMT6-C-15W\***

\*120-277V, 0-10V dimming only

QuickShip option is available on orders of 100 pieces or less, and will ship within 2 business days of the order being received. QuickShip lead time may vary for orders greater than 100 pieces. No additional shipment rates apply. Subject to availability. For additional options please consult your Liteline representative. Due to our continued efforts to improve our products, product specifications are subject to change without notice. Refer to liteline.com for up to date specifications. Color swatches may not be exact, contact rep for sample.



 **Liteline**

Liteline Corporation  
Copyright © 2023  
All rights reserved.

Telephone  
416.996.1856  
1.866.730.7704

Fax  
905.709.5255  
1.888.738.9736

[LITELINE.COM](https://www.liteline.com)

REV 06.12.2023  
M-SLMMULTI-ALL-SS-E

