



UPC Code : 078477290309

Country Of Origin : Mexico

9800

Medium Base, One-Piece, Candle Sockets, Incandescent, Fiber Disc Lampholder, , Single Circuit, Back Wired, - Brown

Technical Information

Material Specifications

Circuit : Single Circuit

Shell Material : Fiber Disc

Termination : 2 Terminal Screws

Voltage : 250 Volt

Wattage Rating : 660W

Mechanical Specifications

Construction : One-Piece

Lamp Socket Base : Medium

Mounting Type : 1/8-27 Adjustable Hickey

Termination : 2 Terminal Screws

Wiring Access : Back Wired

Product Features

Availability : Distribution

Circuit : Single Circuit

Color : Brown

Construction : One-Piece

Lamp Base : Medium

Lamp Socket Base : Medium

Lampholder Type : Candle Socket

Light Type : Incandescent

Mounting Type : 1/8-27 Adjustable Hickey

Screw Shell Material : Aluminum

Shell Material : Fiber Disc

Standards and Certifications

: UL

Termination : 2 Terminal Screws

Voltage : 250 Volt

Warranty : 1 Year Limited

Wattage Rating : 660W

Wiring Access : Back Wired

Standards and Certifications

UL Listed : File E3810

\$(wiring_diagram)

\$(dimensional_drawing)

SPECIFICATION SUBMITTAL

JOB NAME:

CATALOG NUMBERS:

<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER: <input type="text"/>	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.

T. Monday-Friday): +1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)

5386- 1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2024 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts

© 2024 Leviton Manufacturing Co., Inc.