

Eaton M22-DRH-G

Catalog Number: M22-DRH-G

Eaton M22 modular pushbutton M22 Modular Pushbutton Operator, 22.5 mm, Extended, Maintained, Non-illuminated, Bezel: Silver, Button: Green, IP67, IP69K, NEMA 4x, 13, 1,000,000 mechanical operations



Photo is representative

General specifications

Product Name	Catalog Number
Eaton M22 modular pushbutton	M22-DRH-G
UPC	Product Length/Depth
786685276137	7 in
Product Height	Product Width
1.5 in	5 in
Product Weight	Warranty
0.04 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
CE Marked	CSA Certified
GoST-R	CCC Marked
Bureau Veritas	Lloyd's Register Certified
Catalog Notes	
Includes contact block mounting adapter.	

defaultTaxonomyAttributeLabel

Type

Pushbutton

Bezel

Silver

Actuator function

Maintained

Button color

Green

Actuator

Extended, button

Illumination

Non-illuminated

Series

M22

Environmental rating

IP67, IP69K, NEMA 4X, NEMA 13

Operating cycles

1 million

Size

22.5 mm

Resources

Brochures

[M22 Pilot Devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Drawings

[M22\(S\)\(M\)-DRH 3D Model Xchange](#)

[M22\(S\)\(M\)-DRH 2D PDF](#)

[M22\(S\)\(M\)-DRH AutoCAD 2D Footprint \(mm\)](#)

[M22\(S\)\(M\)-DRH AutoCAD 2D Footprint](#)

[M22\(S\)\(M\)-DRH 3D Inventor](#)

[M22\(S\)\(M\)-DRH 2D Drawing Xchange](#)

Installation instructions

[M22 Operators and Accessories](#)

Specifications and datasheets

[Eaton Specification Sheet - M22-DRH-G](#)

[Global Data Sheet - M22-DRH-G](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)