



Pulse Start Metal Halide Standard

MS320/U/PS 12PK

Philips Pulse Start Metal Halide Lamps offer an optimized metal halide system for greater efficiency and lumen maintenance.

Warnings and Safety

• R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Product data


General Information		Warm-up time to 60% light	<120 s
Cap-Base	E39 [Single Contact Mogul Screw]		
		Controls and Dimming	
Light Technical		Dimmable	No
uminous Flux	19,500 lm		
Luminous Efficacy (rated) (Nom)	93.8 lm/W	Mechanical and Housing	
Chromaticity Coordinate X (Nom)	0.395	Bulb Finish	Clear
Chromaticity Coordinate Y (Nom)	0.405	Bulb Material	Hard Glass
Correlated Color Temperature (Nom)	3600 K	Bulb Shape	ED28
Luminous Efficacy (Rated) (Min)	84.4 lm/W		·
Color rendering index (CRI)	>65	Approval and Application	
		Mercury (Hg) Content (Max)	32 mg
Operating and Electrical			·
Power Consumption	320 W	Product Data	
Wattage Equivalent	320 W	Order product name	MS320/U/PS 12PK
		Full product name	MS320/U/PS 12PK

Pulse Start Metal Halide Standard

Order code	383810
Material Nr. (12NC)	928601152503
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.001 kg
EAN/UPC - Product/Case	046677383817

Numerator - Packs per outer box	12
EAN/UPC - Case	50046677383812

Dimensional drawing



Product	D (max)	C (max)
MS320/U/PS 12PK	91 mm	206 mm



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, May 15 - data subject to change