

Project:		Type:
Drawn by:	Catalogue #:	Date:

SLG-2L

"EASY OUT" PLASTIC COMPACT BATTERY UNIT

(Over 4 hours Duration Standalone Unit) 2 x 2 W Crisp White LED Heads

The commercial SLG-2L features a plastic battery unit designed to provide an economical and versatile solution to emergency lighting needs within a small and compact design. The SLG-2L series is configured with two 2 W LED heads and can run for 4 hours duration as a standalone unit.

FEATURES AND SPECIFICATIONS

• Circuitry

- 120/347VAC 60Hz Input, field selectable
- Solid state variable rate charger
- Over 4 hours Duration Standalone Unit
- Momentary push button test switch
- Pilot LED for AC ON and CHARGE status
- Fully automatic, current limited charger
- Short circuit protection
- Complete battery recharge in 24 hours
- Maintenance free, sealed lead acid battery

Mechanical

- High impact, UV stabilized, thermoplastic construction
- 2 x 2 W Crisp White LED Heads
- Low profile, canopy type design with extremely small total footprint
- Universal spider knockout pattern and keyhole mounting slots stamped into back of cabinet
- Unit "quick snaps" onto backplate for simple, speedy installation
- White color is standard

Note: Not intended for flush ceiling mount.

Approval

- CSA Certified to C22.2 #141-15

Compliance

- Meets requirements of ICES-005



ලුකු	QUICKSHI
&_P)	QUICKSHI



ICES 005





OVERVIEW		
Light source	LED	
Input voltage (VAC)	120 / 347	
Emergency duration	Over 4 hours	

For complete warranty details, please see our terms and conditions on our website.



QUICK SHIP AND TECHNICAL SPECIFICATION TABLE : 1

Part number	DC Volts	Watts	Nbr of heads	Head	Lamp	Light source	Input Volts	Color
	(VDC)	(W)			(W)		(VAC)	
SLG-2L	N/A	N/A	2	N	2	LED	120/347	White

¹ QUICK SHIP: Product availability is subject to change without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

ORDERING GUIDE

SLG-2L			
	Series		
SLG-2L			

WIREGUARD²


Part number	Dimensions (in)
WGD630-V2	15.25 x 12.25 x 9.00


 $^{^{\}rm 2}$ Please contact your Stanpro customer service representative for more information.

LEXAN GUARD

	Part number	Dimensions (in)	
Wall Mount	PGD110	14 x 5.75 x 10	

DIMENSIONS





Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.

