



# LED Corn Cobs

## 36CC/LED/850/ND E26 G2 BB 6/1

Philips Corn Cob LED replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	850 [CCT of 5000K]
Luminous Flux	5,400 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	150.00 lm/W
Color Consistency	ANSI 5000K quadrangle
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	36 W
Lamp Current (Nom)	400 mA
Starting Time (Nom)	1 s

Warm-up time to 60% light	1 s
Power Factor (Fraction)	0.9
Voltage (Nom)	100-277 V
UL Type	HIB_UL Type B (UL Listed+Classified)
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	60 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	Corncob
Approval and Application	
Energy Consumption kWh/1000 h	36 kWh
Application Conditions	
can it be used in closed luminaires	Yes


# LED Corn Cobs

## Product Data

Order product name	36CC/LED/850/ND E26 G2 BB 6/1
Full product name	36CC/LED/850/ND E26 G2 BB 6/1
Order code	559716
Material Nr. (12NC)	929002396004
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	046677559717
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677559712

## Dimensional drawing




Product	D	C
36CC/LED/850/ND E26 G2 BB 6/1	85 mm	201 mm


## Photometric data



General uniform lighting - 36CC/LED/850/ND E26 G2 BB 6/1



Light Distribution Diagram - 36CC/LED/850/ND E26 G2 BB 6/1



Spectral Power Distribution Colour - 36CC/LED/850/ND E26 G2 BB 6/1

# LED Corn Cobs

## Lifetime



Life Expectancy Diagram - 36CC/LED/850/ND E26 G2 BB 6/1

Lumen Maintenance Diagram - 36CC/LED/850/ND E26 G2 BB 6/1

