



DIN Rail Utility Box

Hubbell's DIN Rail Utility Box offers a labor saving way to provide utility power to any control cabinet. Installing the DIN Rail Utility Box is as easy as snapping the box onto a 35mm DIN Rail and connecting the line, neutral and ground wires to the terminal block. Utility power for fans, lights, laptop computers, testers or any other power requirement. If load limiting is a concern, Hubbell's "CB" version comes with a 5 Amp circuit breaker that provides over-current protection to make sure that large loads are not drawn from the DIN Rail Utility Box. All Hubbell DIN Rail Utility Boxes may be mounted either vertically or horizontally on the DIN Rail; the "H" version comes with the terminal block mounted for easy wiring when the DIN Rail Utility Box is mounted horizontally.



Duplex Receptacles

Description	Color	Catalog Number	
Complete unit.	Gray	DRUB15	DRUB20
Complete unit, horizontal mount.	Gray	DRUB15H	-
Complete unit with 5A circuit breaker.	Gray	DRUB15CB5	-
Complete unit with 5A circuit breaker, horizontal.	Gray	DRUB15HCB5	-
Complete unit with aux.	Gray	-	DRUB20AC
Complete unit with aux and 5A circuit breaker.	Gray	-	DRUB20ACCB5
Complete unit with NEMA® 6-20R duplex (250V).	Gray	-	DRUB5462*

GFCI Duplex Receptacles

Description	Color	Catalog Number	
Complete unit.	Gray	DRUBGFI15	DRUBGFI20
Complete unit, horizontal.	Gray	DRUBGFI15H	-
Complete unit with 5A circuit breaker.	Gray	DRUBGFI15CB5	-
Complete unit with 5A circuit breaker, horizontal.	Gray	DRUBGFI15HCB5	-
Complete unit with aux GFCI contacts.	Gray	DRUBGFI15AC	DRUBGFI20AC
Complete unit, faceless with aux GFCI contacts.	Gray	-	DRUBGFI20BFAC

TVSS Duplex Receptacles

Description	Color	Catalog Number	
Complete unit.	Gray	DRUBTVSS15	-
Complete unit with aux contacts.	Gray	DRUBTVSS15AC	-

Isolated Ground^Δ Duplex Receptacles

Description	Color	Catalog Number	
Complete unit.	Gray	DRUBIG15	-

Toggle Switch Unit

Description	Color	Catalog Number
Complete unit with HBL1221.	Gray	DRUB1221AC
Complete unit with 15A 125V SW/REC.	Gray	DRUB6404






DIN Rail Utility Box Components

Description	Color	Catalog Number
Pre-wired kit without circuit breaker.	Gray	DRUBKIT
Pre-wired kit with circuit breaker.	Gray	DRUBKITCB5
Pre-wired kit with aux.	Gray	DRUBKITAC
Pre-wired kit with circuit breaker and aux.	Gray	DRUBKITACCB5
Communications kit (unloaded).	Gray	HIDRUBCKIT
(For use with Network Wiring frames in section W).		
Switch plate only.	Gray	KP1GY**
Rectangular opening plate only.	Gray	KP26GY**
1.60 in. opening plate only.	Gray	KP720GY**
1.40 in. opening plate only.	Gray	KP7GY**
Duplex receptacle plate only.	Gray	KP8GY**

Note: ^ΔSee section M for additional information on isolated ground devices.

*DRUB5462 configuration not pictured.

**UL Listed, CSA Certified.



NEMA® is a registered trademark of the National Electrical Manufacturers Association.

Dimensions in Inches (mm)