



LED Corn Cobs

36CC/LED/840/ND E26 G2 BB 6/1

Philips Corn Cob LED replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	5,200 lm
Color Designation	Cool White (CW)
Luminous Efficacy (rated) (Nom)	144.00 lm/W
Correlated Color Temperature (Nom)	4000 K
Color Consistency	ANSI 4000K quadrangle
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	36 W
Lamp Current (Nom)	400 mA
Starting Time (Nom)	1 s
Warm-up time to 60% light	1 s

Power Factor (Fraction)	0.9
Voltage (Nom)	100-277 V
UL Type	HIB_UL Type B (UL Listed+Classified)
Temperature	
Ambient temperature range	-4 °F to 113 °F
T-Case Maximum (Nom)	140 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	Corncob
Approval and Application	
Energy Consumption kWh/1000 h	36 kWh
EU RoHS compliant	Yes
Application Conditions	
can it be used in closed luminaires	Yes


LED Corn Cobs

Product Data

Order product name	36CC/LED/840/ND E26 G2 BB 6/1
Full product name	36CC/LED/840/ND E26 G2 BB 6/1
Order code	559708
Material Nr. (12NC)	929002395904
Numerator - Quantity Per Pack	1



Net Weight (Piece)	1.376 lb
EAN/UPC - Product/Case	046677559700
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677559705

Dimensional drawing




Product	D	C
36CC/LED/840/ND E26 G2 BB 6/1	3-3/8 inch	7-15/16 inch

Photometric data



General uniform lighting - 36CC/LED/840/ND E26 G2 BB 6/1



Light Distribution Diagram - 36CC/LED/840/ND E26 G2 BB 6/1



Spectral Power Distribution Colour - 36CC/LED/840/ND E26 G2 BB 6/1

LED Corn Cobs

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - 36CC/LED/840/ND E26 G2 BB 6/1

