

**2024 Specification Sheet - English**

---



**LONG DESCRIPTION –**

---

**Long Description Marketing Copy**

Oil-tempered spring steel for excellent fishing performance. Dirt-free tape finish keeps hands cleaner during use. Advanced comfort handle grip reduces fatigue. Superior rapid tape pay-out and rewind

**PRODUCT NAME –**

---

**Page Title**

Fishtape, STEEL-240' (BULK PACK)

**PRODUCT OVERVIEW –**

---

**Marketing Text 1**

Oil-tempered spring steel for excellent fishing performance

**Marketing Text 2**

Dirt-free tape finish keeps hands cleaner during use

**Marketing Text 3**

Advanced comfort handle grip reduces fatigue

**Marketing Text 4**

Superior rapid tape pay-out and rewind

**Marketing Text 5**

Smaller Fish Eye with offset bend for improved fishing ability

### **Marketing Text 6**

Improved low profile tip for easy fishing through all sizes of conduit

### **Marketing Text 7**

Viewing Port gives visibility to remaining tape and ability to remove jobsite debris quickly

### **Marketing Text 8**

Rugged case design improves drop impact capability

### **Marketing Text 9**

Flared case with Grip Ridges for no slip handling

### **Marketing Text 10**

Fish tapes are available in 50 FT (15

### **Marketing Text 11**

2 m), 65 FT (19

### **Marketing Text 12**

8 m), 125 FT (38

### **Marketing Text 13**

1 m) and 240 FT (73

### **Marketing Text 14**

2 m) lengths

### **Marketing Text 15**

1/8 IN, 1/4 IN and flat steel profiles to accommodate different fishing situations

## **PRODUCT SPECIFICATION –**

---

### **Product Specification 1**

Sub Brand Name Name : MagnumPRO

### **Product Specification 2**

Package : 3/PACK

### **Product Specification 3**

Tensile Strength : 400.000 LB (1.700 KN) Maximum Design Strength

### **Product Specification 4**

Material : Steel

### **Product Specification 5**

Accessory : R438B Swivel Ball Head for use on 1/8 IN Steel Fish Tapes, R438-BM Ball Tip Male Half, 439-1 12 IN (305 MM) Flexible Fish Tape Leader, 439-2 12 IN (305 MM) SPEED FLEX Leader (solder joints)

### **Product Specification 6**

Application : For Excellent Fishing Performance

**Product Specification 7**

Replacement Part : RS438-240 Replacement Steel Tape - 240 FT (NO CASE), 10051G 8-1/2 IN Case/Handle

Replacement Kit, 10052 12 IN Case/Handle Replacement Kit