









control wire tap for flat busbar connection accessory for: 3VA53/54; 3VA63/64

Model	
product brand name	SETRON
product designation	control wire tap
accessories	Control wire tap
General technical data	
designation / of the terminal	CW-tap for Busbar
type of electrical connection / with control wire tap	Yes
Connections according IEC	
tightening torque / when using copper cables	
<ul style="list-style-type: none"> • solid 	0.75 - 2.5 mm ² : 2 Nm
<ul style="list-style-type: none"> • finely stranded 	0.75 - 2.5 mm ² : 2 Nm
Connections according UL	
permissible temperature / of connectable conductor / according to UL 486A-486B	75 °C
stripped length	0.2-0.3 in
connectable conductor cross-section	
<ul style="list-style-type: none"> • for copper cable / solid / minimum 	18 AWG
<ul style="list-style-type: none"> • for copper cable / solid / maximum 	14 AWG
<ul style="list-style-type: none"> • for copper cable / stranded / minimum 	18 AWG
<ul style="list-style-type: none"> • for copper cable / stranded / maximum 	14 AWG
tightening torque / when using copper cables	
<ul style="list-style-type: none"> • solid 	18 - 14 AWG: 17.7 lb-in
<ul style="list-style-type: none"> • stranded 	18 - 14 AWG: 17.7 lb-in

Certificates

General Product Approval					EMV
 EG-Konf.		 UL	Miscellaneous		 RCM

Marine / Shipping	other	Environment
-------------------	-------	-------------

 LRS	Miscellaneous	Confirmation	Miscellaneous	Environmental Con- firmations	Environmental Con- firmations
--	-------------------------------	------------------------------	-------------------------------	---	---

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9470-0WC00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9470-0WC00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9470-0WC00

CAx-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

8/9/2024 

