

IMPORTANT SAFETY INSTRUCTIONS






When installing or using the lighting system, basic safety precautions should always be followed, including the following:

1. Read all instructions before attempting to install this item.
2. Do not install this lighting system in a damp or wet location.
3. Do not cut any track sections.
4. Do not install any part of a track system less than five (5) feet above the floor.
5. Do not install any fixture assembly closer than six (6) inches from any curtain, or similar combustible material.
6. Disconnect electrical power before adding to or changing the configuration of the track.
7. Do not attempt to energize anything other than lighting track fixtures on the track. To reduce the risk of fire and electric shock, do not attempt to connect power tools, extension cords, appliances, and the like to the track.

INSTALLATION INSTRUCTIONS

1. Before attaching track to ceiling, connect ground clip to track at place where track will rest over ceiling outlet box as in diagram A. Press down to secure ground clip to track with thumb as in diagram B. Contact between clip and track is made by sharp points on the clip which scratch through the paint and contact the metal of the track.
2. Attach track to ceiling or wall using screws supplied.
3. Remove connector block from canopy by unscrewing centre screw in canopy.
4. Place connector block on the track opposite of the ground clip as shown in diagram C. The locking tab should be on the side of track with smooth surface (opposite side with raised rib).
5. Turn connector block in direction of arrow 90° (ON) until locking tab locks in place facing the groove in track as in diagram D. Resistance while turning is normal.
6. Connect wires on connector block and ground clip with corresponding coloured wires in ceiling outlet box.
7. Place canopy over connector block. Small notch as in diagram E should fit over raised rib on track. Secure with screw.

FOR USE WITH GALLERY TRACK SYSTEM ONLY.



DIRECTIVES DE SÉCURITÉ IMPORTANTES
Des précautions élémentaires, dont les suivantes, doivent être prises lors de l'installation et de l'utilisation d'un appareil d'éclairage:

1. Lisez toutes les directives avant d'installer cette appareil.
2. N'installez pas l'appareil d'éclairage dans un endroit humide ou détrempe.
3. Ne coupez pas les sections de rail.
4. Toute partie du rail d'éclairage doit se trouver au moins 1,5 m (5 pi) du sol.
5. Toute lampe doit se trouver au moins 15 cm (6 po) des rideaux ou de toute autre matière combustible du genre.
6. Coupez l'alimentation du secteur avant d'ajouter un rail ou d'en modifier la configuration.
7. Ne branchez rien d'autre que les lampes pour rail d'éclairage sur les rails. Pour réduire le risque d'incendie ou de choc électrique, ne connectez jamais d'outil électrique, de rallonge, d'électroménager ou autres du genre sur le rail.

DIRECTIVES D'INSTALLATION

1. Avant de fixer le rail au plafond, poser l'agrafe de terre sur le rail, au point de rencontre entre le rail et la boîte électrique (schéma A). Insérer l'agrafe sur le rail en ressant (schéma B). Le contact entre l'agrafe et le rail est assuré par des griffes sur l'agrafe qui égratignent la peinture pour toucher au métal du rail.
2. Fixer le rail au plafond ou au mur à l'aide des vis fournies.
3. Séparer la boîte de connexion de l'applique en enlevant la vis au centre de l'applique.
4. Placer la boîte de connexion sur le rail, à l'opposé de l'agrafe de terre (schéma C). La patte d'attache devrait se trouver sur le côté lisse du rail (à l'opposé du rebord surélevé).
5. Tourner la boîte de connexion sur 90° dans le sens de la flèche jusqu'à ce que les pattes d'attache soient face au cheminement (schéma D). Il est normal qu'on s'ente un résistance en tournant.
6. Connecter les fils du boîtier de connexion et de l'agrafe de terre avec les fils de couleurs correspondantes dans la boîte électrique du plafond.
7. Placer l'applique sur le boîtier de connexion. La petite encoche (schéma E) convient au rebord surélevé du rail. Fixer avec la vis.

NE CONVIENT QU'AU RAIL D'ÉCLAIRAGE GALLERY.