

2024 Specification Sheet - English

**LONG DESCRIPTION –**

Long Description Marketing Copy

Equipped with Bluetooth™ Communication enabled via the Greenlee Gator Eye app.. Features LED display screen communicating pressure and battery levels as well as tool diagnostics with real-time tool feedback.. Intelligent Crimping System Technology includes a pressure sensor that monitors the crimping force of each crimp and provides the operator with a visual and audible alert if the force is below specifications. State of the art 18V lithium ion (Li-ion) battery provides 70% more cycles per charge and faster cycle times

PRODUCT NAME –

Page Title

4 Ton Crimper, Li-Ion, standard, 230V

PRODUCT OVERVIEW –

Marketing Text 1

Equipped with Bluetooth™ Communication enabled via the Greenlee Gator Eye app.

Marketing Text 2

Features LED display screen communicating pressure and battery levels as well as tool diagnostics with real-time tool feedback.

Marketing Text 3

Intelligent Crimping System Technology includes a pressure sensor that monitors the crimping force of each crimp and provides the operator with a visual and audible alert if the force is below specifications

Marketing Text 4

State of the art 18V lithium ion (Li-ion) battery provides 70% more cycles per charge and faster cycle times

Marketing Text 5

LED light provides the operator with the battery charge and tool maintenance status

Marketing Text 6

In-Line tool style is lightweight and very easy to control

Marketing Text 7

One trigger controls all tool functions

Marketing Text 8

Crimping head rotates 350°

Marketing Text 9

Tools automatically retract when the crimping cycle is complete

Marketing Text 10

Overmolded tacky grip areas make gripping the tool easier and more comfortable

Marketing Text 11

LED work light illuminates dark work areas

Marketing Text 12

Greenlee battery-powered crimping tools now use bio-degradable oil

Marketing Text 13

Smart chargers control the charging current, charging voltage and battery temperature to maximize battery life

Marketing Text 14

Used with Greenlee KC4, KA4 and KD4 crimping dies

Marketing Text 15

Available with 120V, 12V or 230V battery charger or with 120V or 230V corded adapter in place of batteries and charger

PRODUCT SPECIFICATION –

Product Specification 1

Sub Brand : Gator

Product Specification 2

Type : Die style crimper

Product Specification 3

Application : 4 Ton Crimping

Product Specification 4

Standard : C/US UL Listed

Product Specification 5

Wire Size : 8 AWG - 300 kcmil Cu

Product Specification 6

Wire Size : 8 AWG - 2/0 kcmil Al

Product Specification 7

Overall Length : 13.25 IN (337mm)

Product Specification 8

Crimping Force : 7,900 lbs. (35 kN)

Product Specification 9

Crimping Capacity : 300 kcmil (MCM) Copper

Product Specification 10

Crimping Capacity : 2/0 AWG Al

Product Specification 11

Connector Type : Color-coded lugs and splices

Product Specification 12

Handle Type : In-Line Style with over molded rubber grip