








circular conduc. terminal TA2.3 2 x 25...150 mm² for 2 cables; 3 units accessory for: 3VA20/21/22

Model		
product brand name	SETRON	
product designation	circular conductor terminal	
accessories	Wire connector	
General technical data		
designation / of the terminal	TA2.3	
type of electrical connection / with control wire tap	No	
Connections according IEC		
connectable conductor cross-section		
<ul style="list-style-type: none"> for copper cable / stranded / minimum for copper cable / stranded / maximum for aluminum cable / stranded / minimum for aluminum cable / stranded / maximum 	25 mm ² 150 mm ² 25 mm ² 150 mm ²	
stripped length	26 / 51 mm	
tightening torque / when using copper cables		
<ul style="list-style-type: none"> stranded finely stranded 	25 - 150 mm ² : 31.1 Nm 25 - 150 mm ² : 31.1 Nm	
Connections according UL		
permissible temperature / of connectable conductor / according to UL 486A-486B	75 °C	
stripped length	1.0 / 2.0 in	
connectable conductor cross-section		
<ul style="list-style-type: none"> for copper cable / stranded / minimum for copper cable / stranded / maximum for aluminum cable / stranded / minimum for aluminum cable / stranded / maximum 	4 AWG 300 kcmil 4 AWG 300 kcmil	
tightening torque / when using copper cables		
<ul style="list-style-type: none"> stranded 	4 AWG - 300 kcmil: 275 lb-in	
Certificates		
General Product Approval	EMV	Marine / Shipping
 EG-Konf.		Miscellaneous
		 RCM
		 LRS
other		Environment
Confirmation	Miscellaneous	Miscellaneous
		Environmental Con- firmations
		Environmental Con- firmations

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9223-0JJ22>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9223-0JJ22>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9223-0JJ22

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

8/9/2024 

