

SLMT6-C-15W

6" SLIMLED MULTI, up to 1170 Lumens, 15 Watt,
Color Selectable
Commercial Recessed Downlighting, 0-10V

Job Information		
Project Name		Type
Location		
Quantity		Date
Contact/Phone		
Notes		

Features

Body

Durable airtight aluminum body with twist-and-lock trim that allows for ease and versatility. White trim included, black and brushed nickel trims sold separately.

LED Characteristics

This general application light fixture features a 15 watt LED module that maintains uniform intensity producing up to 1170 lumens; with a typical CRI of 90. CCT select switch 2700 K (default) - 5000 K color temperature.

Dimming

100%-10% dimming capability. This fixture is compatible with industry standard 0-10V dimmers. For compatible dimmers, visit www.liteline.com/SlimLEDMulti

Beam Spread

The fixture lens provides 110° beam spread.

Mounting

Can be mounted to an industry standard 4" octagon box (JBox / standard slab

box) with minimum depth of 1.5" (40mm) via mounting holes.

Compatible Recessed Housings

- RF601CAT series
- RF602ICAT series

LED Driver

Built-in on board driver with 120V AC input.

Quick Connect push-in terminals

"Quick connect" push-in terminals for fast and easy wiring.

Operating Temperature

-30°C~45°C (-22°F~113°F)

Environment

- Suitable for wet locations.
- Fire-rated when used in a fire-rated octagon box.
- Indoor/Outdoor rated.


SPECIFICATION	
Application	Recessed / Surface-mount Downlight
Approved Location	Wet
Beam Angle	110°
CCT	2700 K / 3000 K / 3500 K / 4000 K / 5000 K
Certification	cETLus
Color	WH
CRI	90
Dimming	Yes
Dimming Tech	0-10V
Energy Star	No
Input	120-277V
LM79	Yes
LM80	Yes
Lumens	1170
Lumens per Watt	Up to 81
Power Factor	0.9
Projected Life	70% @ 50,000 hrs
Title 24	Yes
Warranty	5-Year
Wattage	15W

CCT	Lumens
2700 K	1050
3000 K	1090
3500 K	1150
4000 K	1170
5000 K	1115



Description

The SlimLED MULTI 6" Commercial is a 15 watt, round downlight for 4" octagon box installation. It is a high-performance, easy to install residential grade downlight solution that offers good light output, energy-efficiency and streamlined design. Suitable for wet locations.



Notes: Accessories are sold separately. For additional options please consult your Liteline representative.
Due to our continued efforts to improve our products, product specifications are subject to change without notice.

Ordering Guide



SLMT6-C-15W

6" SLIMLED MULTI color selectable round downlight, 15W, with white trim.

Accessories



SLMT6-RT-BK

Optional trim for 6" SlimLED Multi, Black.



SLMT6-RT-BN

Optional trim for 6" SlimLED Multi,
Brushed Nickel.