



# VM4LC13030 - VM4LC Series LED High Bay/ Low Bay, Hazardous Rated 130 Watt, 120-277 VAC 5000K, 20415 Lumens

By Killark  
Catalog # [VM4LC13030](#)



The VM4L Series is a low bay and high bay fixture using energy efficient LED's. The design of the VM4LB with the bulb style heat sink creates a light distribution similar to a HID lamp. The design of the VM4LC with the concave style heat sink creates a light distribution with no up light. This fixture is made with a cast copper-free aluminum housing and mount that is suitable for harsh and hazardous environments. With the design of this fixtures internal heat sink keeps a clean look on the outside of the fixture creating a LED fixture that does not contain external heat fins.

## Application

Certilite® V VM4L LED fixtures are designed for installations where moisture, dirt, dust, corrosion and vibration may be present, or NEMA 3 and 4X areas where wind, water, snow or high ambients can be expected. They can be used in locations made hazardous by the presence of flammable vapors or gases or combustible dusts as defined by the NEC/CEC

## General

Catalog Number	VM4LC13030
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Light Source	LED
Lumen Range	15,001-25,000 lm
Lumens	17820
Mounting Type	Luminaire Only
Optic Type	Luminaire Only
Series	VM4L
UPC	783936082516

## Electrical Ratings

Current Rating	60 A
Frequency Rating	50/60 Hz
Lumens Per Watt	137.1
Voltage Rating	120-277 VAC

Wattage 130 W

## Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none"><li>Class I, Division 2, Groups A, B, C, D</li><li>Class I, Zone 2, Groups IIC, IIB, IIA</li><li>Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>Class III, Divisions 1 &amp; 2</li></ul>
---------------------	---

## Logistics

Carton Quantity 1

## Product Assets

- [Certifications - VM4L Series Luminaires CSA Cert](#)
- [Certifications - VMLX/VM4L Series ATEX Certificate](#)
- [Certifications - VMLX/VM4L Series EU Type ATEX Certificate](#)
- [Certifications - VMLX & VM4L Series IECEx Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - VM4L Series LED Luminaires IOM K1462](#)
- [Specifications - VM4LC13030 Specification Sheet French](#)
- [Specifications - VM LED Fixture Assembly Guide](#)
- [Specifications - VM2L/VM4L Series High Wattage Specification Sheet](#)